



Heat Shrink Tubing > Single Wall DR 25: Heat Shrink Tubing, 2:1 Shrink Ratio

Primary Product Color: **Black**Wall Type: **Single**Expanded Inside Diameter (Min): **9.53 mm [.375 in]**Recovered Inside Diameter (Max): **4.8 mm [.189 in]**Shrink Ratio: **2:1**[All Single Wall DR 25: Heat Shrink Tubing, 2:1 Shrink Ratio \(11\)](#)

Features

Product Type Features

Wall Type	Single
-----------	--------

Body Features

Material Systems Code	25
Fluid Type	Aviation Fuel, Brake Fluid, Diesel Fuel, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Crosslinked Elastomer
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Nominal)	1.02 mm[.04 in]
Expanded Inside Diameter (Min)	9.53 mm[.375 in]
Recovered Inside Diameter (Max)	4.8 mm[.189 in]
Heat Shrink Tubing Size Range	4.8 – 9.53 mm[.189 – .375 in]

Usage Conditions

Shrink Temperature (Min)	175 °C
Fluid Resistance	Splash Protection



Heat Shrink Tubing Flammability	Flame-Retardant
Operating Temperature Range	-75 – 150 °C
Heat Shrink Tubing Resistance	Abrasion, Fluids, Mechanical Damage, Strain Relief
Recovery Temperature	175 °C

Product Availability

Applicable Region	Worldwide
-------------------	-----------

Packaging Features

Packaging Method	Reel
------------------	------

Other

Product Source	UK
----------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V

Documents

Product Drawings

[DR-25-3/8-0-SP](#)

English

Datasheets & Catalog Pages

[1654025_Sec3_DR-25](#)

English

[Harness Repair Products Quick Reference Guide](#)

English

Product Specifications

[Product Specification](#)

English

Product Environmental Compliance

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English