

RNF-100-1/8-X-SP

✓ ACTIVE

RAYCHEM | RAYCHEM RNF-100

TE Internal #: 5070044032

Heat Shrink Tubing, Clear, Single Wall, .125 in [3.2 mm] Expanded Inside, .062 in [1.6 mm] Recovered Inside, 2:1 Shrink Ratio, RAYCHEM RNF-100

[View on TE.com >](#)



Heat Shrink Tubing



Primary Product Color: **Clear**

Wall Type: **Single**

Expanded Inside Diameter (Min): **3.2 mm [.125 in]**

Recovered Inside Diameter (Max): **1.6 mm [.062 in]**

Shrink Ratio: **2:1**

Features

Product Type Features

Product Family	RNF-100
Wall Type	Single

Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

Body Features

Fluid Type	Gasoline, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Clear
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Tolerance)	.2 mm[.008 in]
Recovered Wall Thickness (Nominal)	.5 mm[.02 in]
Expanded Inside Diameter (Min)	3.2 mm[.125 in]
Recovered Inside Diameter (Max)	1.6 mm[.062 in]
Heat Shrink Tubing Size Range	1.6 – 3.2 mm[.062 – .125 in]

Usage Conditions

--



Shrink Temperature (Min)	95 °C
Fluid Resistance	Splash Protection
Heat Shrink Tubing Flammability	Non-Flame-Retardant
Operating Temperature Range	-55 – 135 °C
Heat Shrink Tubing Resistance	Abrasion, Fluids, Mechanical Damage, Strain Relief
Recovery Temperature	121 °C

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Box
------------------	-----

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | RAYCHEM RNF-100



Heat Shrink Tubing(985)



Power Cable Tubing & Accessories(8)

Documents

Datasheets & Catalog Pages
RNF-100 Pages from 9-1773447-9

English

Product Specifications
Quality Specification

English

Product Environmental Compliance
Safety Datasheet

English

Safety Datasheet
English

Safety Datasheet

Safety Datasheet

Safety Datasheet
English

Safety Datasheet
French

Safety Datasheet
German

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet
English



[Safety Datasheet](#)