

EET-1325G-4 ✓ ACTIVE


TE Internal #: 4-1768018-1

Standard Labels, Label Width 25.4 mm [1 in], Label Height .5 in [12.7 mm], Yellow, Polyamide, Label Thickness 104 Micron

[View on TE.com >](#)



Identification & Labeling > Labels > Standard Labels



Label Type: **Blank Labels**

Label Style: **Die-Cut**

Label Adhesive Type: **Permanent**

UL Listed: **No**

Label Width: **25.4 mm [1 in]**

Features

Product Type Features

Label Type	Blank Labels
------------	--------------

Body Features

Label Color	Yellow
-------------	--------

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------

Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
---------------------	--

Recommended Printer Ribbon	See Printer Ribbon Matrix
----------------------------	---------------------------

Printer Technology	Thermal Transfer
--------------------	------------------

Label Style	Die-Cut
-------------	---------

Label Width	25.4 mm[1 in]
-------------	---------------

Label Height	12.7 mm[.5 in]
--------------	----------------

Label Material	Polyamide
----------------	-----------

Label Thickness	104 Micron
-----------------	------------

Industry Standards

UL Listed	No
-----------	----

Packaging Features

Packaging Quantity	10000
--------------------	-------

Other

Label Adhesive Type	Permanent
---------------------	-----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2019 (197) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1768018-4
EET-0920G-4

Documents

Product Drawings

[EET-1325G-4](#)

English



Datasheets & Catalog Pages

[EET-G-4_THERMAL_TRANSFER_LABELS](#)

English

Product Specifications

[IDENTIFICATION PRINTER PRODUCT RIBBON MATRIX](#)

English