

505079-1 ✓ ACTIVE

AMPLIVAR

TE Internal #: 505079-1

Ring Terminals & Spade Terminals, Ring Tongue, 16 – 13 AWG

Wire Size, 1.25 – 2.5 mm² Wire Size, 2600 – 4900 CMA Wire Size,

Stud Size #10, AMPLIVAR

[View on TE.com >](#)



Terminals & Splices > Ring Terminals & Spade Terminals



Ring & Spade Terminal Type: **Ring Tongue**

Wire Size: **2600 – 4900 CMA**

Stud Size: **#10**

Features

Product Type Features

Terminal Features	Sheared
Shape Description	RING-037
Stud Size	#10
Sealable	No
Compatible With Discrete Wire Type	Magnet Wire
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	180 °

Body Features

Inspection Slot	No
Weight per Piece	.643 g

Contact Features

Ring & Spade Terminal Type	Ring Tongue
Barrel Type	Open



Terminal Orientation	Straight
Terminal Plating Material	Unplated
Contact Underplating Material	Brass

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	2600 – 4900 CMA
Stud Diameter	4.82 mm[.19 in]
Tongue Thickness	.5 mm[.02 in]
Overall Product Length	30.98 mm[1.22 in]
Barrel Inside Diameter	2.29 mm[.09 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Compatible With Wire Base Material	Aluminum, Copper
Heavy Duty	No

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	8000
Packaging Method	Strip

Other

Comment	Stud Retaining Terminal
---------	-------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224)



Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 63147-1
AMVAR RING 13 1/2-17 020BR

TE Part # 640212-1
AMVAR R 13-11 #10 025TPBR

TE Part # 9556824001
DWTC-4/1-X-SP

TE Part # 485044-1
RING AMVAR 18-14 IS 8 028LUBZ

TE Part # 350571-1
AMVAR R 13-11 180STD 025TPBR



TE Part # 485079-1
RING AMVAR 18-14 IS 8 028 LUBZ

TE Part # 505036-1
AMVAR R 2 14.5MAG PTPBR

TE Part # 505044-1
STUD RTNG AMVAR TERM .020 BR



Also in the Series | AMPLIVAR



Documents

Product Drawings

STUD RETAINING TERM.

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_505079-1_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_505079-1_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_505079-1_D.3d_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English