




RAYCHEM | RAYCHEM RT-3

TE Internal #: 5202062019

Heat Shrink Tubing, Black, Single Wall, .24 in [6.1 mm] Expanded Inside, .095 in [2.4 mm] Recovered Inside, 2.5:1 Shrink Ratio, RAYCHEM RT-3

[View on TE.com >](#)

Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Single**

Expanded Inside Diameter (Min): **6.1 mm [.24 in]**

Recovered Inside Diameter (Max): **2.4 mm [.095 in]**

Shrink Ratio: **2.5:1**

Features

Product Type Features

Product Family	RT-3
Wall Type	Single

Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

Body Features

Fluid Type	Aviation Fuel, Chemicals/Solvents, Water
Primary Product Color	Black
Shrink Ratio	2.5:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Semi-Rigid

Dimensions

Recovered Wall Thickness (Tolerance)	.79 mm[.031 in]
Cut Length	1220 mm[48 – 49 in]
Expanded Inside Diameter (Min)	6.1 mm[.24 in]
Recovered Inside Diameter (Max)	2.4 mm[.095 in]

Usage Conditions

Shrink Temperature (Min)	110 °C
Heat Shrink Tubing Flammability	Flame-Retardant



Operating Temperature Range	-55 – 135 °C
Heat Shrink Tubing Resistance	Abrasion, Fluids, Mechanical Damage, Strain Relief
Recovery Temperature	135 °C

Product Availability

Applicable Region	Americas, Asia
-------------------	----------------

Packaging Features

Packaging Method	Stick
------------------	-------

Other

Meets Low Outgassing Requirements	No
Product Source	US

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | RAYCHEM RT-3



Documents

Product Drawings

RT-3-NO.1-0-STK

English

Datasheets & Catalog Pages

RT-3 Pages from 9-1773447-9

English

Semirigid, Flame-Retardant Polyolefin Heat-Shrinkable Tubing

English

Product Specifications

Quality Specification

English