




TE Internal #: 5212044-1

DIN Connectors, Circular DIN, Receptacle, Wire-to-Board, 5 Position, Selectively Loaded, Mating Alignment, Keyed Mating Alignment Type

[View on TE.com >](#)

Connectors > Circular Connectors > DIN Connectors



Circular DIN Connector Type: **Circular DIN**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **5**

Connector Contact Load Condition: **Selectively Loaded**

Features

Product Type Features

ESD Protection	Without
Circular DIN Connector Type	Circular DIN
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Type	Header
Shape	Circular
Shielded	Yes
Strain Relief	With
Wire/Cable Type	Discrete Wire
Product Type	Connector

Configuration Features

Number of Positions	5
Connector Contact Load Condition	Selectively Loaded



PCB Mount Orientation	Right Angle
Electrical Characteristics	
Hot Pluggable	No
Operating Voltage	250 VAC
Body Features	
Shield Underplate Material	Nickel
Shield Plating Thickness	2.54 µm[100 µin]
Shield Underplate Thickness	1.27 µm[50 µin]
Shield Plating Material	Tin/Nickel
Shield Material	Brass
Contact Features	
Contact Layout	Staggered
Contact Underplating Material	Nickel
Reverse Gender	No
Contact Base Material	Brass
Contact Current Rating (Max)	7.5 A
Contact Design	Tuning Fork
Contact Termination Area Plating Material	Tin
Contact Type	Socket
Contact Transmits (Typical)	Power, Signal (Data), Signal (Data)/Power
Contact Mating Area Plating Thickness	2.54 µm[100 µin]
Contact Mating Area Plating Material	Tin
Contact Termination Area Plating Thickness	2.54 µm[100 µin]
Termination Features	
Termination Method to Printed Circuit Board	Through Hole - Solder
Mechanical Attachment	
PCB Mount Alignment Type	Solder Tail Layout
PCB Mount Alignment	With
Panel Mount Feature	Without
Mating Alignment	With
Mating Alignment Type	Keyed
PCB Mount Retention	With



PCB Mount Retention Type	Kinked Legs
Connector Mounting Type	Board Mount
Mating Retention	Without

Housing Features

Centerline (Pitch)	2.49 mm[.1 in]
Housing Color	Black
Housing Material	Nylon

Dimensions

Width	15.49 mm[.61 in]
Tail Length	3.56 mm[.14 in]
Length	21.84 mm[.86 in]
Height	20.83 mm[.82 in]
PCB Thickness (Recommended)	2.36 mm

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

CSA File Number	LR 3507
VDE Tested	No
Agency/Standard	CSA, UL
UL Rating	Recognized
UL File Number	E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Gang of Tubes
Packaging Quantity	100

Other

Comment	For applications requiring a 3-position connector, use a 5-position connector (contact positions 4 and 5 not used).
---------	---

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5212032-1
4 CIRC DIN RCPT GRND SHLD



TE Part # 5520842-1
5 CIRC DIN RCPT,GRND SHIELD



TE Part # 5212045-1
6 CIRC DIN RCPT GRND SHLD

Documents

Product Drawings
5 CIRC DIN RCPT GRND SHLD

English

CAD Files
3D PDF

3D



Customer View Model

[ENG_CVM_CVM_5212044-1_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5212044-1_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5212044-1_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Agency Approvals

[Agency Approval Document](#)

English