

TE Internal #: 5535653-1
 PCMCIA Connectors, Fully Shrouded, 68 Position, .05 in [1.27 mm]
 Centerline, 4 Row, 1 Card Slots, Through Hole - Solder Mount,
 Right Angle

[View on TE.com >](#)



[Connectors](#) > [PCB Connectors](#) > [Memory Card Connectors](#) > [PCMCIA Connectors](#)



Header Type: **Fully Shrouded**

Number of Positions: **68**

Centerline (Pitch): **1.27 mm [.05 in]**

Number of Rows: **4**

Number of Card Slots: **1**

Features

Product Type Features

Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	68
Number of Rows	4
Number of Card Slots	1
PCB Mount Orientation	Right Angle

Contact Features

Contact Current Rating (Max)	.5 A
------------------------------	------

Mechanical Attachment

PCB Mounting Style	Through Hole - Solder
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	1.27 mm[.05 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-20 – 70 °C
-----------------------------	-------------

Operation/Application



Circuit Application	Signal
---------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 5146321-1 68 MEMCD HDR STD T/H ENHNCD</p>	 <p>TE Part # 5535651-1 68 MEM CARD HDR STD SMT TOP</p>	 <p>TE Part # 5535655-2 68 MEMCD HDR RSD T/H TOP LV</p>	 <p>TE Part # 5535651-6 68 MEMCD HDR STD SMT TOP LV, N</p>
--	--	--	---



Documents

Product Drawings

[68 MEM CARD HDR STD T/H TOP](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_5535653-1_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5535653-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5535653-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English