



CHAMP | CHAMP Docking Connectors

TE Internal #: 5554349-1

IDC D-Sub Connectors, Receptacle, 30 – 26 AWG Solid Wire Size, .05 – .13 mm<sup>2</sup> Solid Wire Size, 28 AWG Stranded Wire, CHAMP Docking Connectors

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors > IDC D-Sub: Receptacle Assembly, Signal, 2.16 mm



Connector & Housing Type: **Receptacle**

Solid Wire Size: **.05 – .13 mm<sup>2</sup>**

Stranded Wire Size: **.08 mm<sup>2</sup>**

[All IDC D-Sub: Receptacle Assembly, Signal, 2.16 mm \(21\)](#)

## Features

### Product Type Features

Connector Classification	IDC
Profile	Standard
Product Category	Connectors
Connector & Housing Type	Receptacle
Connector System	Cable-to-Panel
Connector Product Type	Connector Assembly
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	24
Number of Rows	2
Compatible With Wire & Cable Type	Ribbon Cable

### Body Features

Strain Relief Clip Material	Thermoplastic
-----------------------------	---------------



Shield Material	Die Cast Metal
-----------------	----------------

Color	Black
-------	-------

Ribbon Cable Centerline Spacing	1.27 mm[.05 in]
---------------------------------	-----------------

Cover Material	Polyphenylene Oxide
----------------	---------------------

Shield Plating Material	Nickel
-------------------------	--------

### Contact Features

Contact Mating Area Plating Material	Gold or Gold Flash over Palladium Nickel
--------------------------------------	--

Contact Underplating Material	Nickel, Palladium Nickel
-------------------------------	--------------------------

PCB Contact Termination Area Plating Material	Gold Flash
---	------------

Contact Base Material	Copper Alloy
-----------------------	--------------

Contact Current Rating (Max)	1 A
------------------------------	-----

### Mechanical Attachment

Mating Connector Lock	With
-----------------------	------

Mating Connector Lock Type	Screwlocks
----------------------------	------------

Panel Mount Feature	Without
---------------------	---------

Connector Mounting Type	Panel Mount
-------------------------	-------------

### Housing Features

Housing Material	Polyphenylene Oxide
------------------	---------------------

Housing Color	Black
---------------	-------

Centerline (Pitch)	2.16 mm[.085 in]
--------------------	------------------

### Dimensions

Solid Wire Size	.05 – .13 mm <sup>2</sup>
-----------------	---------------------------

Stranded Wire Size	.08 mm <sup>2</sup>
--------------------	---------------------

Wire Size	28 AWG
-----------	--------

### Usage Conditions

Operating Temperature Range	-40 – 75 °C[-40 – 167 °F]
-----------------------------	---------------------------

### Operation/Application

Shielded	Yes
----------	-----

Circuit Application	Signal
---------------------	--------

### Packaging Features

Packaging Method	Package
------------------	---------

Packaging Quantity	50
--------------------	----

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



Also in the Series | [CHAMP Docking Connectors](#)



D-Sub Covers(28)



D-Sub Locking &amp; Mounting(29)



Docking Connector Guide Hardware(5)



Docking Connectors(31)



IDC D-Sub Connectors(79)



PCB D-Sub Connectors(1)

## Documents

### Product Drawings

#### EMI RCPT ASSY, 24 POS, SHLD

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5554349-1\\_B.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5554349-1\\_B.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5554349-1\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

#### Product Specification

English

### Product Environmental Compliance

#### TE Material Declaration

English