



Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**
Ratchet Configuration: **Not Releasable, Not Adjustable**
Die Sets Type: **Fixed In Tool**
Specification Type: **MIL Spec, TE Product Specification (114-), UL/CSA**
TE Certification: **Yes – Certificate Included**

Features

Other

| | |
|-----------------------------|--|
| Crimp Form-Wire Barrel Type | Closed Barrel - Confined Crescent |
| Tool Grade | Premium Crimp Tooling |
| Ratchet Configuration | Not Releasable, Not Adjustable |
| Die Sets Type | Fixed In Tool |
| Specification Type | MIL Spec, TE Product Specification (114-), UL/CSA |
| TE Certification | Yes – Certificate Included |
| Power Technology Type | Battery, Manual |
| Tooling Type | Double Action Hand Tool |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Out of Scope |
| EU ELV Directive 2000/53/EC | Out of Scope |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Not reviewed for China RoHS compliance |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC |















| | |
|---------------------------|---|
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

| | | | |
|--|---|---|---|
|  <p>TE Part # CAT-P592-F614 PIDG Flanged Spade Tongue Terminals</p> |  <p>TE Part # CAT-P592-SH816 PIDG Short Spring Spade Tongue Terminals</p> |  <p>TE Part # CAT-P592-R472A PIDG RING TONGUE TERMINALS</p> |  <p>TE Part # CAT-P592-K742 PIDG Knife Disconnect Splices</p> |
|  <p>TE Part # CAT-P592-SP118 PIDG Spade Tongue Terminals</p> |  <p>TE Part # CAT-P592-L853 PIDG Long Spring Spade Tongue Terminals</p> |  <p>TE Part # CAT-P592-F266 PIDG FASTON Receptacle Quick Disconnects</p> |  <p>TE Part # CAT-P592-SL56 PIDG Slotted Ring Tongue Terminals</p> |
|  <p>TE Part # 165142 PIDG WIRE PIN 22-16</p> |  <p>TE Part # CAT-P592-R2456 PIDG Rectangular Tongue Terminals</p> |  <p>TE Part # 34313 PIDG HK 22-16 COMM 22-18 MIL 6</p> |  <p>TE Part # 66023-2 TAB,PIDG TERMI-BK 22-16</p> |



| | | | |
|---|--|---|---|
|  <p>TE Part # 34152 PG R 22-16 COMM 22-18 MIL 3/8</p> |  <p>TE Part # 53240-1 PG SP SPD 22-16COMM22-18MIL 6</p> |  <p>TE Part # 34149 PG R 22-16 COMM 22-18 MIL 10</p> |  <p>TE Part # 34155 PG SPD 22-16 COMM 22-18 MIL 8</p> |
|  <p>TE Part # 52454 PG SPR SPD 22-16COMM 22-18MIL8</p> |  <p>TE Part # 320665 PG SPD 22-16 COMM 22-18 MIL 6</p> |  <p>TE Part # 52949 PG SPR SPD 22-16COMM 22-18MIL6</p> |  <p>TE Part # 52947 PG SP SPD 22-16COMM 22-18MIL 4</p> |

Documents

Datasheets & Catalog Pages

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (non U.S.)

English