



Connectors > PCB Connectors > Backplane Connectors > Eurocard Connectors



Connector & Housing Type: **Receptacle**
Connector System: **Board-to-Board**
Termination Post & Tail Length: **2.79 mm [.11 in]**
Number of Positions: **64**
Centerline (Pitch): **2.54 mm [.1 in]**

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
DIN Size	Half
DIN Level	II

Configuration Features

Number of Positions	64
Number of Rows	3
PCB Mount Orientation	Right Angle
Number of Columns	32
Number of Signal Positions	64
Rows Loaded	A, C

Electrical Characteristics



Operating Voltage	250 VAC
-------------------	---------

Contact Features

Contact Cross Section	.25 x .25 mm[.01 x .01 in]
PCB Contact Termination Area Plating Material Thickness	2.54 µm[100 µin]
Contact Type	Socket
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Mating Area Plating Material	Gold
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	1.5 A

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Post & Tail Length	2.79 mm[.11 in]

Mechanical Attachment

Mating Retention	Without
Mating Alignment	Without
PCB Mount Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	With
PCB Mount Retention Type	Boardlock
Connector Mounting Type	Board Mount

Housing Features

Housing Material	Polymer - GF
Housing Color	Gray
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Connector Height	10.49 mm[.413 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]
Row-to-Row Spacing	2.54 mm[.1 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application



Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




 TE Part # 5650945-5 ASSY,PIN,EUROCARD,TYPE C,LEAD-	 TE Part # 650934-5 064 EURO TYPE R PIN ST ASSY	 TE Part # 5650933-5 ASSY,PIN,EUROCARD,TYPE R,LEAD-	 TE Part # 9-1393644-4 V42254B1200C963=PC612 MESSERLE
 TE Part # 9-1393640-3 V42254B2201C963=PC612 FEDERLEI	 TE Part # 5650951-5 ASSY,PIN,EUROCARD,TYPE C,LEAD-	 TE Part # 5650870-5 ASSEMBLY,RECEPTACLE,EURO,TYPE	 TE Part # 5535059-4 ASSY,RECEPTACLE,EURO,TYPE C,L-FREE,A&C,6
 TE Part # 650408-5 064 EURO TYPE C RECEPT ST ASSY	 TE Part # 1-650930-4 064 EURO TYPE R PIN AP ASSY	 TE Part # 5536356-5 ASSY,PIN,EUROCARD,"C",LEAD-FREE,A&C,64/9	 TE Part # 5650956-5 ASSEMBLY,RECEPTACLE,EURO,TYPE
 TE Part # 650458-5 064 EURO TYPE C RECEPT ST ASSY	 TE Part # 650945-5 064 EURO TYPE C PIN ST ASSY	 TE Part # 1-148167-5 064 EURO TYP C RECP 13MM ASSY	 TE Part # 536098-5 064 EURO TYP R PIN AP MFBL ASY
 TE Part # 5650912-5 ASSY,PIN,EUROCARD,TYPE R,LEAD-FREE,A&C,6	 TE Part # 650933-5 064 EURO TYPE R PIN ST ASSY	 TE Part # 650951-5 064 EURO TYPE C PIN ST ASSY	 TE Part # 2-1393640-5 V42254B2102C963=PC612 FEDERLEI

Also in the Series | Eurocard Type R



Eurocard Connectors(92)



Standard Edge Connectors(1)

Documents

Product Drawings

ASSY,RECEPT,EURO,TYPE R,L-FREE,A&C,64/96

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5650897-4_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5650897-4_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5650897-4_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English