

5747958-1 ✓ ACTIVE




AMPLIMITE

TE Internal #: 5747958-1

Crimp D-Sub Connectors, Plug, Cable-to-Cable, 37 Position, Size 20, Size 4, Mating Retention, Shielded

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Connectors > Crimp D-Sub Connectors > D-Sub Crimp: Plug, Signal, 37 Posn, Pin Size 20, Shell Size 4



Connector & Housing Type: **Plug**

Connector System: **Cable-to-Cable**

Number of Positions: **37**

D-Sub Contact Size: **20**

D-Sub Shell Size: **4**

[All D-Sub Crimp: Plug, Signal, 37 Posn, Pin Size 20, Shell Size 4 \(7\)](#)

Features

Product Type Features

Grounding Indents	With
Product Type	Connector
Grade	Standard
Shell Type	Full Metal Shell
Connector & Housing Type	Plug
Connector System	Cable-to-Cable
D-Sub Shell Size	4
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	37
---------------------	----

Body Features

Shell Plating Material	Tin over Copper
------------------------	-----------------



Shield Plating Material	Tin
-------------------------	-----

Shell Material	Steel
----------------	-------

Shield Material	Steel
-----------------	-------

Insert Material	Glass Filled Nylon/Polyester
-----------------	------------------------------

Contact Features

D-Sub Contact Size	20
--------------------	----

Mechanical Attachment

Jackscrew Material	Zinc Alloy
--------------------	------------

Mating Retention	With
------------------	------

Mating Retention Type	Jackscrews
-----------------------	------------

Housing Features

Housing Color	Black
---------------	-------

Housing Material	Nylon GF
------------------	----------

Centerline (Pitch)	2.74 mm, 2.76 mm, 2.79 mm [.108 in][.109 in] [.11 in]
--------------------	--

Dimensions

Cable Insulation Diameter Range	8.59 – 14.28 mm
---------------------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Shielded	Yes
----------	-----

Circuit Application	Signal
---------------------	--------

Industry Standards

Insert Flammability Rating	UL 94V-0
----------------------------	----------

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1
--------------------	---

Packaging Method	Kit, Package
------------------	--------------

Other

Comment	Maximum cable diameter after jacket and braid removed., Plugs accept size 20 DF
---------	---

pin contacts., There is a maximum Cable O. D. of 14.27 [.562] for Shielding Enclosure Expansion Tool 58241-2.

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # CAT-035-DCRSS204 D-Sub Crimp Recpt Signal 37 Posn, Socket Size 20, Shell Size 4</p>	 <p>TE Part # CAT-035-DCPPS204 D-Sub Crimp: Plug, Signal, 37 Posn, Pin Size 20, Shell Size 4</p>
--	---

Documents

Product Drawings

[KIT,PLUG,37P,HDP-20,SHLD ENCLS](#)



English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_5747958-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5747958-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5747958-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Cable Connectors](#)

English

[AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_5747958-1_040620181019_dmtec](#)

English

[MD_5747958-1_040620181019_dmtec](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English