



RAYCHEM | RAYCHEM LSTT

TE Internal #: 5426974001

Heat Shrink Tubing, Black, Single Wall, 1 in [25.4 mm] Expanded Inside, .5 in [12.7 mm] Recovered Inside, 2:1 Shrink Ratio, RAYCHEM LSTT

[View on TE.com >](#)

Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Single**

Expanded Inside Diameter (Min): **25.4 mm [1 in]**

Recovered Inside Diameter (Max): **12.7 mm [.5 in]**

Shrink Ratio: **2:1**

Features

Product Type Features

| | |
|----------------|--------|
| Product Family | LSTT |
| Wall Type | Single |

Electrical Characteristics

| | |
|---------------|-------|
| Voltage (Max) | .6 kV |
|---------------|-------|

Body Features

| | |
|--------------------------|--|
| Fluid Type | Antifreeze, Battery Acid, Diesel Fuel, Gasoline, Hydraulic Fluid, Lubricating Oil, Water |
| Primary Product Color | Black |
| Shrink Ratio | 2:1 |
| Primary Product Material | Irradiated Modified Polyolefin |
| Flexibility | Very Flexible |

Dimensions

| | |
|--------------------------------------|---------------------------|
| Recovered Wall Thickness (Tolerance) | .15 mm[.006 in] |
| Recovered Wall Thickness (Nominal) | .95 mm[.037 in] |
| Expanded Inside Diameter (Min) | 25.4 mm[1 in] |
| Recovered Inside Diameter (Max) | 12.7 mm[.5 in] |
| Heat Shrink Tubing Size Range | 12.7 – 25.4 mm[.5 – 1 in] |

Usage Conditions



| | |
|---------------------------------|---------------------|
| Shrink Temperature (Min) | 65 °C |
| Fluid Resistance | Splash Protection |
| Heat Shrink Tubing Flammability | Non-Flame-Retardant |
| Operating Temperature Range | -40 – 125 °C |
| Heat Shrink Tubing Resistance | Mechanical Damage |
| Recovery Temperature | 110 °C |

Product Availability

| | |
|-------------------|--------|
| Applicable Region | Global |
|-------------------|--------|

Packaging Features

| | |
|------------------|------|
| Packaging Method | Reel |
|------------------|------|

Other

| | |
|-----------------------------------|----------------|
| Meets Low Outgassing Requirements | No |
| Product Source | Czech Republic |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC |
| Halogen Content | BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources. |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM LSTT



Heat Shrink Tubing(150)

Documents

Product Drawings

[LSTT-25.4-0-SP](#)

English

Datasheets & Catalog Pages

[LSTT Pages from 9-1773447-9](#)

English

Product Specifications

[Quality Specification](#)

English

Product Environmental Compliance

[Safety Datasheet](#)

English

[Safety Datasheet](#)

English

[Safety Datasheet](#)

[Safety Datasheet](#)



[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)