

5788795-1 ✓ ACTIVE



AMPLIMITE


TE Internal #: 5788795-1

PCB D-Sub Connectors, Plug, Board-to-Board, 25 Position, 2.28 mm [.089 in] Centerline, 2 Row, Size 1, Round, Standard Profile, Right Angle

[View on TE.com >](#)

[Connectors >](#) [D-Shaped Connectors >](#) [D-Sub Connectors >](#) [PCB D-Sub Connectors >](#)

D-Sub Plug Assembly: Standard, Right Angle, Shell Size 1, 2.74mm



Connector & Housing Type: **Plug**

Connector System: **Board-to-Board**

Number of Positions: **25**

Centerline (Pitch): **2.28 mm [.089 in]**

Number of Rows: **2**

[All D-Sub Plug Assembly: Standard, Right Angle, Shell Size 1, 2.74mm \(53\)](#)

Features

Product Type Features

| | |
|-----------------------------------|-----------------------|
| Grounding Indents | With |
| Grounding Straps | With |
| Footprint | 8.08 mm[.318 in] |
| Shell Type | Front Metal Shell |
| Connector & Housing Type | Plug |
| Connector System | Board-to-Board |
| D-Sub Shell Size | 1 |
| Sealable | No |
| Connector & Contact Terminates To | Printed Circuit Board |
| Product Type | Connector |

Configuration Features

| | |
|---------------------|----|
| Number of Positions | 25 |
|---------------------|----|



| | |
|-----------------------|-------------|
| Number of Rows | 2 |
| PCB Mount Orientation | Right Angle |
| Preloaded | Yes |

Body Features

| | |
|-----------------------------------|----------------|
| Eyelet Material | Brass |
| Eyelet Plating Material | Tin |
| Female Screwlock Material | Zinc |
| Plastic | No |
| Female Screwlock Plating Material | Clear Chromate |
| Connector Profile | Standard |
| Shell Plating Material | Tin |
| Shell Material | Steel |
| | .026 in |

Contact Features

| | |
|---|-----------------|
| Contact Mating Area Plating Material | Gold |
| Contact Underplating Material | Nickel |
| PCB Contact Termination Area Plating Material | Tin |
| Contact Base Material | Phosphor Bronze |
| Contact Shape & Form | Round |
| Contact Current Rating (Max) | 6 A |
| | 30 μ m |

Termination Features

| | |
|---|-----------------------|
| Grounding Clips | Without |
| Termination Method to Printed Circuit Board | Through Hole - Solder |
| Termination Post Length | 3.18 mm [.125 in] |

Mechanical Attachment

| | |
|--------------------------|--------------------------|
| PCB Mount Alignment | With |
| Panel Mount Feature | Without |
| PCB Mount Retention | With |
| PCB Mount Retention Type | Boardlock |
| Mating Retention | With |
| Mating Retention Type | Female Screwlocks, Fixed |



| | |
|----------------------------|--------------|
| Connector Mounting Type | Board Mount |
| Boardlock Plating Material | Tin |
| Boardlock Material | Copper Alloy |
| Mating Alignment | With |

Housing Features

| | |
|--------------------|-------------------|
| Centerline (Pitch) | 2.28 mm [.089 in] |
| Housing Material | Thermoplastic |
| Housing Color | Black |

Dimensions

| | |
|-----------------------------|-------------------|
| Row-to-Row Spacing | 2.84 mm [.112 in] |
| PCB Thickness (Recommended) | 1.57 mm [.062 in] |

Usage Conditions

| | |
|-----------------------------|-----------------------------|
| High Temperature Housing | Yes |
| Operating Temperature Range | -55 – 105 °C [-67 – 221 °F] |

Operation/Application

| | |
|---------------------|--------|
| Circuit Application | Signal |
|---------------------|--------|

Industry Standards

| | |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Packaging Features

| | |
|--------------------|---------|
| Packaging Method | Package |
| Packaging Quantity | 65 |

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-023-DRARS3277
D-Sub Receptacle Assembly: Right Angle, Shell Size 3, 2.77mm



TE Part # CAT-AM7-248H5
IDC D-Sub: Receptacle Assembly, Wire to Wire, Signal, 2.77 mm



TE Part # CAT-AM7-253
IDC D-Sub: Receptacle Assembly, Low Profile, Signal, 2.77 mm



TE Part # CAT-AM7-248H6
IDC D-Sub: Receptacle Kit, Wire to Wire, Signal, 2.74 mm



TE Part # 747548-8
KIT, RCPT, 25P, HDE, SHLD HDWRE

Documents

Product Drawings

[25 HTMSFL PLUG RA 318 \(SL,BL\)](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_5788795-1_C.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5788795-1_C.3d_igs.zip](#)



English

Customer View Model

[ENG_CVM_CVM_5788795-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Right-Angle Posted Connectors](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English