



RAYCHEM | RAYCHEM QS1500

TE Internal #: 581913P005

Heat Shrink Tubing, Black, Dual Wall, .3 in [7.62 mm] Expanded Inside, .065 in [1.65 mm] Recovered Inside, 4:1 Shrink Ratio, RAYCHEM QS1500

[View on TE.com >](#)

Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Dual**

Expanded Inside Diameter (Min): **7.62 mm [.3 in]**

Recovered Inside Diameter (Max): **1.65 mm [.065 in]**

Shrink Ratio: **4:1**

Features

Product Type Features

Product Family	QS1500
Wall Type	Dual

Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

Body Features

Fluid Type	Water
Primary Product Color	Black
Shrink Ratio	4:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Tolerance)	1.52 mm[.06 in]
Cut Length	45 mm[1.77 in]
Expanded Inside Diameter (Min)	7.62 mm[.3 in]
Recovered Inside Diameter (Max)	1.65 mm[.065 in]

Usage Conditions

Shrink Temperature (Min)	70 °C
Heat Shrink Tubing Flammability	Flame-Retardant



Operating Temperature Range	-40 – 110 °C
Heat Shrink Tubing Resistance	Abrasion
Recovery Temperature	121 °C

Product Availability

Applicable Region	Americas
-------------------	----------

Packaging Features

Packaging Method	Piece
------------------	-------

Other

Meets Low Outgassing Requirements	No
Product Source	US

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | **RAYCHEM QS1500**



Heat Shrink Tubing(37)

Documents

Product Drawings

[QS1500-NO.2-F6-0-45MM](#)

English

Datasheets & Catalog Pages

[Measuring_Single_Wall_Tubing](#)

English

[Selecting_Correct_Tubing](#)

English

Product Specifications

[Quality Specification](#)

English

Product Environmental Compliance

[Safety Datasheet](#)

English

[Safety Datasheet](#)

English

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

QS1500-NO.2-F6-0-45MM

Heat Shrink Tubing, Black, Dual Wall, .3 in [7.62 mm] Expanded Inside, .065 in [1.65 mm] Recovered Inside, 4:1 Shrink Ratio, RAYCHEM QS1500



English

[Safety Datasheet](#)