



Application Tooling > Hand Crimping Tools



TE Certification: **Cannot be Certified**

Power Technology Type: **Manual, Pneumatic**

Tooling Type: **Head Assembly**

### Features

#### Other

Crimp Form-Wire Barrel Type	Insulation Displacement
TE Certification	Cannot be Certified
Power Technology Type	Manual, Pneumatic
Tooling Type	Head Assembly

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 <p>TE Part # CAT-104MTA-NTPNR MTA Receptacle: Nylon, Tin Plated, 2.54 mm</p>	 <p>TE Part # CAT-104MTA-NTPMR Nylon Tin Plated Receptacle: 2.54 mm, with Mating Alignment, MTA 100</p>	 <p>TE Part # CAT-104MTA-NGPNR Nylon Gold Plated Receptacle: 2.54 mm, no Mating Alignment</p>	 <p>TE Part # CAT-104MTA-NGPMR Nylon Gold Plated Receptacle: 2.54 mm, with Mating Alignment, MTA 100</p>
 <p>TE Part # 58074-1 MTA 50/100/156 MANUAL TOOL FRAME</p>	 <p>TE Part # 58075-1 MTA 50/100/156 PNEUMATIC TOOL FRAME</p>	 <p>TE Part # 3-647080-2 02P MTA100 CONN ASSY ON TAPE</p>	 <p>TE Part # 3-647080-3 03P MTA100 CONN ASSY ON TAPE</p>
 <p>TE Part # 3-647080-5 05P MTA100 CONN ASSY ON TAPE</p>	 <p>TE Part # 647080-2 02P MTA100 CONN ASSY ON TAPE</p>	 <p>TE Part # 647080-3 03P MTA100 CONN ASSY ON TAPE</p>	 <p>TE Part # 3-644314-4 04P MTA100 CONN ASSY 30AU</p>
 <p>TE Part # 3-644314-5 05P MTA100 CONN ASSY 30AU</p>	 <p>TE Part # 3-644314-6 06P MTA100 CONN ASSY 30AU</p>		

## Documents

[Datasheets & Catalog Pages](#)  
[MTA Portable Tooling Solutions](#)

English



## [Bottoming Dies](#)

English

---

## [Instruction Sheets](#)

### [Instruction Sheet \(U.S.\)](#)

English

### [Ribbon Cable Terminating Head 58256-3 for MTA .100 Receptacle Connectors](#)

English

### [Instruction Sheet \(U.S.\)](#)

English