



Connectors > D-Shaped Connectors > D-Sub Connectors > PCB D-Sub Connectors



Connector & Housing Type: **Receptacle**

Number of Positions: **14**

Centerline (Pitch): **1.27 mm [.05 in]**

Number of Rows: **4**

Row-to-Row Spacing: **1.9 mm [.075 in]**

Features

Product Type Features

Shell Type	Front Metal Shell
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Printed Circuit Board
Connector Type	Header
Product Type	Connector

Configuration Features

Number of Positions	14
Number of Rows	4
PCB Mount Orientation	Right Angle
Preloaded	Yes

Body Features

Tine Plate Material	PBT
Front Shell Plating Material	Nickel over Copper
Front Shell Material	Steel
Connector Profile	Standard
Post Size	.32 mm
Color	Black
Shell Material	Steel
Shell Plating Material	Nickel over Copper

Contact Features

Contact Mating Area Plating Material	Gold
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy

Termination Features

Termination Post Length	3.1 mm[.122 in]
-------------------------	-----------------

Mechanical Attachment

Panel Mount Feature	With
PCB Mount Retention	With
PCB Mount Retention Type	Boardlock
Mating Retention	With
Mating Retention Type	Latches
Mounting Angle	Right Angle
Mounting Hole Diameter	2.7 mm

Housing Features

Centerline (Pitch)	1.27 mm[.05 in]
Housing Material	PBT
Housing Color	Black

Dimensions

Row-to-Row Spacing	1.9 mm[.075 in]
PCB Thickness (Recommended)	1.66 mm

Usage Conditions

Housing Material Temperature	Standard
------------------------------	----------

Packaging Features

Packaging Method	Tray
Packaging Quantity	150

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Documents

Product Drawings

[CHAMP 050 FMS RE HDR ASY 14P](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_5917738-1_O.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5917738-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5917738-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.