

5554217-4 ✓ ACTIVE

CHAMP

TE Internal #: 5554217-4

PCB D-Sub Connectors, Receptacle, Cable-to-Board, 50 Position,  
2.16 mm [.085 in] Centerline, 2 Row, Standard Profile, Vertical, PCB  
Mount Retention

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connectors > PCB D-Sub Connectors > D-Sub Shielded Receptacle Assembly: Vertical, 2.16mm



Connector & Housing Type: **Receptacle**

Connector System: **Cable-to-Board**

Number of Positions: **50**

Centerline (Pitch): **2.16 mm [.085 in]**

Number of Rows: **2**

[All D-Sub Shielded Receptacle Assembly: Vertical, 2.16mm \(4\)](#)

### Features

#### Product Type Features

Grounded	No
Boss on Shield	With
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Shielded	Yes
Product Type	Connector
Orientation	Standard

#### Configuration Features

Number of Positions	50
Number of Rows	2
PCB Mount Orientation	Vertical



Preloaded	Yes
-----------	-----

### Body Features

Connector Profile	Standard
-------------------	----------

Color	Black
-------	-------

Shield Material	Die Cast Metal
-----------------	----------------

Shield Plating Material	Nickel
-------------------------	--------

### Contact Features

Contact Mating Area Plating Material	Gold Flash over Palladium Nickel
--------------------------------------	----------------------------------

Contact Underplating Material	Palladium Nickel
-------------------------------	------------------

PCB Contact Termination Area Plating Material	Tin
---	-----

Contact Base Material	Phosphor Bronze
-----------------------	-----------------

	30 μin
--	--------

### Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Termination Post Length	4.7 mm[.185 in]
-------------------------	-----------------

### Mechanical Attachment

Panel Attachment Style	Rear Mount
------------------------	------------

Panel Mount Feature	With
---------------------	------

PCB Mount Retention	With
---------------------	------

PCB Mount Retention Type	Mounting Hole
--------------------------	---------------

Mating Retention	With
------------------	------

Mating Retention Type	Screwlocks
-----------------------	------------

Connector Mounting Type	Board Mount
-------------------------	-------------

Screw Size	14702
------------	-------

	.152 in
--	---------

### Housing Features

Centerline (Pitch)	2.16 mm[.085 in]
--------------------	------------------

Housing Material	Thermoplastic
------------------	---------------

Housing Color	Black
---------------	-------

### Dimensions

Row-to-Row Spacing	4.3 mm[.169 in]
--------------------	-----------------

### Usage Conditions



Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	Signal
---------------------	--------

### Packaging Features

Packaging Method	Tray
------------------	------

Packaging Quantity	60
--------------------	----

### Other

Comment	SCSI applicable with Bail Lock Hardware Kit P/N 554818-2.
---------	---

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
--	---

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Wave solder capable to 265°C
---------------------------	------------------------------

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Documents

### Product Drawings



**RCPT ASSY,50 POS,VERT MTG,SHLD**

English

---

**CAD Files**

**3D PDF**

English

**Customer View Model**

[ENG\\_CVM\\_5554217-4\\_A.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_5554217-4\\_A.3d\\_stp.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_5554217-4\\_A.2d\\_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Product Environmental Compliance**

[MD\\_5554217-4\\_12132016649\\_dmtec](#)

English

[MD\\_5554217-4\\_12132016649\\_dmtec](#)

English