




Connectors > D-Shaped Connectors > D-Sub Connectors > PCB D-Sub Connectors > D-Sub Shielded Receptacle Assembly: Vertical, 2.16mm



Connector & Housing Type: **Receptacle**

Connector System: **Cable-to-Board**

Number of Positions: **24**

Centerline (Pitch): **2.16 mm [.085 in]**

Number of Rows: **2**

[All D-Sub Shielded Receptacle Assembly: Vertical, 2.16mm \(4\)](#)

Features

Product Type Features

Grounded	No
Boss on Shield	With
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Shielded	Yes
Product Type	Connector
Orientation	Standard

Configuration Features

Number of Positions	24
Number of Rows	2
PCB Mount Orientation	Vertical



Preloaded	Yes
Body Features	
Connector Profile	Standard
Color	Black
Shield Material	Die Cast Metal
Shield Plating Material	Nickel
Contact Features	
Contact Mating Area Plating Material	Gold Flash over Palladium Nickel
Contact Underplating Material	Palladium Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
	30 µin
Termination Features	
Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Post Length	3.81 mm[.15 in]
Mechanical Attachment	
Panel Attachment Style	Rear Mount
Panel Mount Feature	With
PCB Mount Retention	With
PCB Mount Retention Type	Mounting Hole
Mating Retention	With
Mating Retention Type	Screwlocks
Connector Mounting Type	Board Mount
Screw Size	11841
Housing Features	
Centerline (Pitch)	2.16 mm[.085 in]
Housing Material	Polyester
Housing Color	Black
Dimensions	
Row-to-Row Spacing	4.3 mm[.169 in]
Usage Conditions	
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]



Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Tray
Packaging Quantity	90

Product Compliance


For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5552243-1
ASSY, PLUG, 64 POS, VERT MTG

Documents

Product Drawings

RCPT ASSY,24 POS,V/M,SCR LK

English

CAD Files

Customer View Model

ENG_CVM_CVM_5554501-1_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5554501-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5554501-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

MD_5554501-1_040320181010_dmtec

English

MD_5554501-1_040320181010_dmtec

English