

RNF-3000-6/2-X-STK ✓ ACTIVE

RAYCHEM | RAYCHEM RNF-3000

TE Internal #: 5677922006

Heat Shrink Tubing, Clear, Single Wall, .236 in [6 mm] Expanded Inside, .079 in [2 mm] Recovered Inside, 3:1 Shrink Ratio, RAYCHEM RNF-3000

[View on TE.com >](#)



Heat Shrink Tubing > RNF-3000 Single Wall Stick Heat Shrink



Primary Product Color: **Clear**

Wall Type: **Single**

Expanded Inside Diameter (Min): **6 mm [.236 in]**

Recovered Inside Diameter (Max): **2 mm [.079 in]**

Shrink Ratio: **3:1**

[All RNF-3000 Single Wall Stick Heat Shrink \(178\)](#)

Features

Product Type Features

| | |
|----------------|----------|
| Product Family | RNF-3000 |
| Wall Type | Single |

Electrical Characteristics

| | |
|---------------|-------|
| Voltage (Max) | .6 kV |
|---------------|-------|

Body Features

| | |
|--------------------------|---|
| Fluid Type | Gasoline, Hydraulic Fluid, Lubricating Oil, Water |
| Primary Product Color | Clear |
| Shrink Ratio | 3:1 |
| Primary Product Material | Irradiated Modified Polyolefin |
| Flexibility | Flexible |

Dimensions

| | |
|--------------------------------------|--------------------|
| Recovered Wall Thickness (Tolerance) | .1 mm[.003 in] |
| Cut Length | 1220 mm[48.031 in] |
| Recovered Wall Thickness (Nominal) | .65 mm[.026 in] |
| Expanded Inside Diameter (Min) | 6 mm[.236 in] |
| Recovered Inside Diameter (Max) | 2 mm[.079 in] |



| | |
|-------------------------------|---------------------------|
| Heat Shrink Tubing Size Range | 2 – 6 mm [.079 – .236 in] |
|-------------------------------|---------------------------|

Usage Conditions

| | |
|---------------------------------|---|
| Shrink Temperature (Min) | 80 °C |
| Fluid Resistance | Splash Protection |
| Heat Shrink Tubing Flammability | Non-Flame-Retardant |
| Operating Temperature Range | -55 – 135 °C |
| Heat Shrink Tubing Resistance | Abrasion, Fluids, Mechanical Damage, Strain Relief |
| Recovery Temperature | 120 °C |

Product Availability

| | |
|-------------------|--------|
| Applicable Region | Global |
|-------------------|--------|

Packaging Features

| | |
|------------------|-------|
| Packaging Method | Stick |
|------------------|-------|

Other

| | |
|-----------------------------------|----------------|
| Meets Low Outgassing Requirements | No |
| Product Source | Czech Republic |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC |
| Halogen Content | BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources. |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM RNF-3000



Heat Shrink Tubing(215)

Documents

Product Drawings

[RNF-3000-6/2-X-STK](#)

English

Datasheets & Catalog Pages

[RNF-3000 Pages from 9-1773447-9](#)

English

[Measuring_Single_Wall_Tubing](#)

English

[Selecting_Correct_Tubing](#)

English

Product Specifications

[Quality Specification](#)

English