




**HOLTITE**

TE Internal #: 5-1437514-9

Pin Sockets, Socket Length 3.96 mm [.156 in], PCB Hole Diameter .082 in [2.08 mm], Open Bottom, .081 – .162 mm<sup>2</sup> Wire Size, 28 – 25 AWG Wire Size

[View on TE.com >](#)

Connectors > Socket Connectors > Pin Sockets



Socket Length: 3.96 mm [.156 in]

PCB Hole Diameter: 2.08 mm [.082 in]

Socket Sleeve Style: **Open Bottom**

Wire Size: .081 – .162 mm<sup>2</sup>

**Features**

**Product Type Features**

Socket Sleeve Style	Open Bottom
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

**Configuration Features**

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

**Body Features**

Sleeve Material	Copper
Sleeve Plating Material	Tin

**Contact Features**

Contact Spring Plating Material	Tin
Contact Mating Area Plating Material Thickness	.76 µm
Contact Mating Area Plating Material	Gold
Contact Base Material	Beryllium Copper



Contact Current Rating (Max)	5 A
------------------------------	-----

### Termination Features

Insertion Method	Hand/Semi-Automatic
Termination Method to Printed Circuit Board	Through Hole - Press-Fit
Termination Method to Wire & Cable	Solder

### Dimensions

PCB Thickness (Recommended)	.79 – 3.18 mm [.03 – .05 in]
Socket Length	3.96 mm [.156 in]
PCB Hole Diameter	2.08 mm [.082 in]
Wire Size	.081 – .162 mm <sup>2</sup>
Mating Pin Diameter Range	.89 – 1.14 mm [.035 – .045 in]

### Usage Conditions

Operating Temperature Range	-65 – 125 °C [-85 – 257 °F]
-----------------------------	-----------------------------

### Operation/Application

Solder Process Feature	None
Circuit Application	Signal

### Packaging Features

Packaging Quantity	2000
Packaging Method	Loose Piece

### Other

Spring Material	Beryllium Copper
-----------------	------------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (.6% in Component Part)

#### Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

## Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


## Solder Process Capability

Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Documents

## CAD Files

## 3D PDF

3D

## Customer View Model

[ENG\\_CVM\\_CVM\\_5-1437514-9\\_C.2d\\_dxf.zip](#)

English

## Customer View Model

[ENG\\_CVM\\_CVM\\_5-1437514-9\\_C.3d\\_igs.zip](#)

English

## Customer View Model

[ENG\\_CVM\\_CVM\\_5-1437514-9\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Product Specifications

[Coaxial High Voltage Connectors](#)



English

[Application Specification](#)

English

[Application Specification](#)

English

---

**Product Environmental Compliance**

[MD\\_5-1437514-9\\_1214201763\\_dmtec](#)

English

[MD\\_5-1437514-9\\_1214201763\\_dmtec](#)

English