




Relays, Contactors & Switches > Switches > Switch Knobs



Switch Knob Product Type: **Knob**
Switch Knob Material: **Molded Phenolic Resin**
Knob Design: **Ribbed**
Shaft Size: **3.17 mm [.125 in]**
Switch Knob Diameter: **11.1 mm [.437 in]**

Features

Product Type Features

Switch Knob Product Type	Knob
--------------------------	------

Configuration Features

Skirt	Without
Spinner	Without
Spin Plate	Without
Knob Design	Ribbed

Body Features

Switch Knob Material	Molded Phenolic Resin
Switch Knob Color	Black

Dimensions

Shaft Size	3.17 mm[.125 in]
Switch Knob Diameter	11.1 mm[.437 in]

Identification Marking

Indicator Style	Line
-----------------	------



Indicator Location	Top & Side
Other	
Comment	Top spun aluminum inlay, Use 4.4 set screw

Product Compliance





For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 5-1437624-0 PKES60B1/4=KNOB PLSTC FLUTED W	 TE Part # 5-1437624-1 PKES60B1/8=KNOB	 TE Part # 5-1437624-2 PKES70B1/4=KNOB FLUTED W/SKIRT	 TE Part # 5-1437624-3 PKES90B1/4=KNOB PLSTC FLUTED W
--	---	--	--



Documents

Product Drawings

PKG40B1/8=KNOB PLASTIC 1/8 LEX

English

CAD Files

Customer View Model

ENG_CVM_5-1437624-9_A.3d_igs.zip

English

Customer View Model

ENG_CVM_5-1437624-9_A.3d_stp.zip

English

Customer View Model

ENG_CVM_5-1437624-9_A.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_CVM_5-1437624-9_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-1437624-9_O.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_5-1437624-9_O.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English

Product Environmental Compliance

Product Compliance



English

Product Compliance

English