




TE Internal #: 5749263-1
 DIN Connectors, Mini DIN, Receptacle, Wire-to-Board, 4 Position,
 Fully Loaded, Mating Alignment, Polarization Mating Alignment
 Type, Right Angle

[View on TE.com >](#)

Connectors > Circular Connectors > DIN Connectors



Circular DIN Connector Type: **Mini DIN**
 Connector & Housing Type: **Receptacle**
 Connector System: **Wire-to-Board**
 Number of Positions: **4**
 Connector Contact Load Condition: **Fully Loaded**

Features

Product Type Features

ESD Protection	Without
Circular DIN Connector Type	Mini DIN
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Type	Header
Shape	Circular
Shielded	Yes
Product Type	Connector

Configuration Features

Stacked	No
Number of Positions	4
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Right Angle



Electrical Characteristics

Operating Voltage	30 VAC
-------------------	--------

Body Features

Outer Shield Material	Brass
Panel Grounding	Without
Panel Ground Feature Type	None
Front Panel Screw-Down	Without
Shield Plating Finish	Bright
Shield Plating Material	Tin
Shield Material	Copper Alloy

Contact Features

PCB Termination Area Plating Finish	Matte
Contact Layout	Staggered
Contact Underplating Material Thickness	1.27 μm [50 μin]
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	.5 A
Contact Design	Tuning Fork
Contact Termination Area Plating Material	Tin
Contact Type	Socket
Contact Transmits (Typical)	Signal (Data)
Contact Mating Area Plating Material	Gold Flash
Contact Termination Area Plating Thickness	3.05 μm , 4.02 μm [120 μin][170 μin]

Termination Features

Grounding Clips	Without
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

PCB Mount Alignment Type	Hold-Down
PCB Mount Alignment	With
Panel Mount Feature	With
Panel Mount Feature Type	Screw Nut



Mating Alignment	With
Mating Alignment Type	Polarization
PCB Mount Retention	Without
PCB Mount Retention Type	Hold-Down Post
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	6.5 mm[.26 in]
Housing Color	Black
Housing Material	Thermoplastic

Dimensions

Width	14 mm[.55 in]
Tail Length	3.18 mm[.125 in]
PCB Tail Length	3.18 mm[.1 in]
Length	12.83 mm[.51 in]
Height	16.51 mm[.65 in]
PCB Thickness (Recommended)	2.68 mm[.11 in]

Usage Conditions

Temperature Rating	High
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

VDE Tested	No
Agency/Standard	CSA, UL
UL Rating	Recognized
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Tube
Packaging Quantity	37

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

Mini DIN, 4 pos, R/A, Shield

English

CAD Files

3D PDF

3D

Customer View Model



[ENG_CVM_CVM_5749263-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5749263-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5749263-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_5749263-1_052020142355_dmtec](#)

English

[MD_5749263-1_052020142355_dmtec](#)

English