

5749699-8 x OBSOLETE

AMPLIMITE | AMPLIMITE 0.50 Series

TE Internal #: 5749699-8

TE Internal Description: 100 50SR CABLE RCPT KIT

IDC D-Sub: Receptacle Kit, Cable to Cable, Signal, 1.27 mm

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors > IDC D-Sub: Receptacle Kit, Cable to Cable, Signal, 1.27 mm



Connector & Housing Type: **Receptacle**

Solid Wire Size: .05 – .1 mm²

Shielded: **Yes**

Connector System: **Cable-to-Cable**

[All IDC D-Sub: Receptacle Kit, Cable to Cable, Signal, 1.27 mm \(4\)](#)

Features

Product Type Features

Rails	Without
Connector & Housing Type	Receptacle
Connector System	Cable-to-Cable
Connector Product Type	Connector Kit
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	100
Number of Rows	2
Compatible With Wire & Cable Type	Round Jacketed Cable

Body Features

Color	Black
	.025 in
Cover Material	Thermoplastic
Plug Shell Plating Material	Tin-Nickel Alloy
Plug Shell Material	Steel
Shell Material	Steel
Shell Plating Material	Nickel over Copper

Contact Features

	30 µin
Contact Mating Area Plating Material	Gold or Gold Flash over Palladium Nickel
Contact Underplating Material	Nickel, Palladium Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	1 A

Termination Features

Termination Cover Type	Standard
Termination Cover Method	Unassembled
Termination Cover	Without
Termination Method to Wire & Cable	Insulation Displacement (IDC)

Mechanical Attachment

Mating Connector Lock	Without
Mounting Angle	None
Panel Mount Feature	Without
PCB Mount Retention Type	None
Detent	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Thermoplastic
Housing Color	Black
Centerline (Pitch)	1.27 mm[.05 in]

Dimensions

Insulation Diameter (Max)	.91 mm
Accepts Wire Insulation Diameter Range	.74 – .91 mm[.029 – .036 in]
Solid Wire Size	.05 – .1 mm ²
Wire Size	.05 – .09 mm ²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	Yes
----------	-----



Circuit Application

Signal

Industry Standards

UL Flammability Rating

UL 94V-0

Cover Flammability Rating

UL 94V-0

Packaging Features

Packaging Method

Kit

Packaging Quantity

7

Other

Comment

Receptacle connector requires backshell kit for complete assembly

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)
 Candidate List Declared Against: JUNE 2022 (224)
 Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [AMPLIMITE 0.50 Series](#)



D-Sub Backshells & Clamps(31)



D-Sub Covers(20)



D-Sub Locking & Mounting(8)



IDC D-Sub Connectors(76)



Insertion & Extraction Tools(1)



PCB D-Sub Connectors(191)

Documents

Product Drawings

100 50SR CABLE RCPT KIT

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5749699-8_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5749699-8_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5749699-8_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - .050 Series Connector

English

AMPLIMITE .050 Series D-sub Connectors QRG

English

Product Specifications

Application Specification

English



Instruction Sheets

Customer Manual (U.S.)

English

Agency Approvals

UL

English