




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **10**

Number of Rows: **1**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Breakaway
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	10
Number of Rows	1
Board-to-Board Configuration	Parallel

Body Features

Connector Profile	Standard
Primary Product Color	Black

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
	100 – 200 μin
Contact Shape & Form	Square



Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin-Lead
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.762 μm[30 μin]
Contact Type	Pin
Contact Current Rating (Max)	3 A

Termination Features

Square Termination Post & Tail Dimension	.64 mm[.025 in]
Termination Post & Tail Length	2.92 mm[.115 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Mating Alignment	With
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
Housing Material	Thermoplastic

Dimensions

PCB Thickness (Recommended)	1.6 mm[.063 in]
-----------------------------	-----------------

Usage Conditions

Housing Temperature Rating	High
Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]

Operation/Application

Solder Process Feature	Board Standoff
Circuit Application	Signal

Industry Standards

Approved Standards	CSA LR7189, UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	25000
--------------------	-------



Packaging Type	Reel
Product Compliance For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-102084-0 112 MODII HORZ DR CE EESS .100	 TE Part # 1-102084-1 110 MODII HORZ DR CE EESS .100	 TE Part # 1-102084-2 108 MODII HORZ DR CE EESS .100	 TE Part # 1-102084-3 106 MODII HORZ DR CE EESS .100
--	---	--	--



TE Part # 1-102084-4
104 MODII HORZ DR CE EESS .100



TE Part # 1-102084-5
102 MODII HORZ DR CE EESS .100



TE Part # 1-102084-6
100 MODII HORZ DR CE EESS .100



TE Part # 1-102084-7
98 MODII HORZ DR CE EESS .100



TE Part # 1-102084-8
96 MODII HORZ DR CE EESS .100



TE Part # 1-102084-9
94 MODII HORZ DR CE EESS .100



TE Part # 1-5102084-0
112 MODII HORZ DR CE EESS .100



TE Part # 1-5102084-1
110 MODII HORZ DR CE EESS .100



TE Part # 1-5102084-2
108 MODII HORZ DR CE EESS .100



TE Part # 1-5102084-3
106 MODII HORZ DR CE EESS .100



TE Part # 1-5102084-4
104 MODII HORZ DR CE EESS .100



TE Part # 1-5102084-5
102 MODII HORZ DR CE EESS .100



TE Part # 1-5102084-6
100 MODII HORZ DR CE EESS .100



TE Part # 1-5102084-7
98 MODII HORZ DR CE EESS .100



TE Part # 1-5102084-8
96 MODII HORZ DR CE EESS .100



TE Part # 1-5102084-9
94 MODII HORZ DR CE EESS .100


Also in the Series | AMPMODU Headers



PCB Connector Mounting(1)



PCB Connector Shrouds(1)



PCB Headers & Receptacles(6830)



PCB Latches, Locks & Retainers(2)



Wire-to-Board Connector Assemblies & Housings(5)



Wire-to-Board Connector Contacts(66)

Documents

Product Drawings

B/A REELED SRST HDR ASSY 30 AU

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-146870-1_C_c-5-146870-1-c.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-146870-1_C_c-5-146870-1-c.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-146870-1_C_c-5-146870-1-c.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION5

English

1-1773720-9_AMPMODU_MOD_IV_V_QRG

English