

5767032-4 ✓ ACTIVE

MICTOR


TE Internal #: 5767032-4

PCB Mount Header, Vertical, Board-to-Board, 152 Position, .64 mm [.025 in] Centerline, Gold, Surface Mount, Signal, Black

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **152**

Centerline (Pitch): **.64 mm [ .025 in ]**

### Features

#### Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

#### Configuration Features

Number of Power Positions	4
Number of Columns	76
Stackable	Yes
Number of Signal Positions	152
PCB Mount Orientation	Vertical
Number of Positions	152
Board-to-Board Configuration	Parallel

#### Electrical Characteristics

Dielectric Withstanding Voltage (Max)	500 VAC
---------------------------------------	---------



Insulation Resistance	2 MΩ
Impedance	152 Ω
Operating Voltage	30 VAC

### Signal Characteristics

Differential Signaling	Yes
Data Rate	10 Gb/s

### Body Features

Primary Product Color	Black
-----------------------	-------

### Contact Features

Contact Layout	Inline
Contact Mating Area Length	1.63 mm[.064 in]
PCB Contact Termination Area Plating Material Thickness	3.81 – 6.35 μm[150 μin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Shape & Form	Dual Beam
Contact Mating Area Plating Material Finish	Matte
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
	29.9212 μin
Contact Type	Pin
Contact Current Rating (Max)	11.5 A

### Termination Features

Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Rectangular Termination Post & Tail Width	.45 mm[.018 in]
Termination Method to Printed Circuit Board	Surface Mount

### Mechanical Attachment

PCB Mount Alignment Type	Locating Posts
Mating Retention	Without
PCB Mount Retention Type	Boardlock
Mating Alignment	With
Mating Alignment Type	Polarized
PCB Mount Retention	With



PCB Mount Alignment	With
Connector Mounting Type	Board Mount

### Housing Features

Mating Entry Location	Top
Centerline (Pitch)	.64 mm [.025 in]
Housing Material	Matte

### Dimensions

Connector Length	63.45 mm [2.498 in]
Connector Height	19.81 mm [.78 in]
Connector Width	8.13 mm [.32 in]
Stack Height	20 mm, 29 mm [.785 in] [1.143 in]

### Usage Conditions

Operating Temperature Range	-55 – 125 °C [-67 – 257 °F]
-----------------------------	-----------------------------

### Operation/Application

Circuit Application	Signal
---------------------	--------

### Industry Standards

UL Rating	Listed
Agency/Standard	CSA, UL
Approved Standards	CSA 1195944, UL E28476
UL Flammability Rating	UL 94V-0

### Packaging Features

Packaging Quantity	8
Packaging Type	Box, Tube

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224)



Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

TE Part # 2-5767004-5  
MICTOR RECEPT ASSY, 152 POS.

TE Part # 5767130-4  
MICT,RCPT,152,ASY,GOLD,EXTD

TE Part # 1-5767096-1  
MICT,REC,152,ASY,.025,TAPE,CAP

TE Part # 1-5767114-1  
MICT,REC,152,ASY,.025,TAPE PKG

TE Part # 1-5767115-1  
MICT,REC,152,ASY,.025 TAPE PKG

TE Part # 1-5767145-1  
MICTOR RECEPTACLE ASSY, .355 V

TE Part # 1-5767146-1  
TAPE AND REEL PACKAGED RECEPTA

TE Part # 1-5767153-1  
152 POS. .355 VERTICAL RECEPTA

TE Part # 5767044-4  
MICTOR,R/A,RECPT,.062,152,ASY


TE Part # 5767054-4  
MICT,RECPT,152,ASSY,PDNI

TE Part # 5767061-4  
MICT,RECPT,152,ASSY,093,PDNI

TE Part # 5767081-4  
MICT,REC,152,ASY,PDNI,BARBLESS



TE Part # 5767089-4  
MICTOR,R/A,RECPT,.093,152,ASY



TE Part # 5767094-4  
MICT,RECPT,152,ASY,PDNI,EXTD



TE Part # 5767095-4  
MICT,REC,EXT,152,ASY,PDNI,025



TE Part # 5767096-4  
MICT,REC,152,ASY,.025,TAPE PKG



TE Part # 5767110-4  
MICT,RECPT,152,ASSY,.025



TE Part # 5767114-4  
MICT,REC,152,ASY,.025,TAPE,CAP



TE Part # 5767115-4  
MICT,REC,152,ASY,.025 TAPE PKG



TE Part # 5767143-4  
MICT,R/A,RCPT,152,ASY,062,30AU

## Documents

### Product Drawings

[MICT,788PLUG,152,ASSY,.025,REC](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_5767032-4\\_B.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5767032-4\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5767032-4\\_B.3d\\_stp.zip](#)

English

[3D PDF](#)

English

Customer View Model

[ENG\\_CVM\\_5767032-4\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_5767032-4\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_5767032-4\\_A.3d\\_stp.zip](#)



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Datasheets & Catalog Pages

### MICTOR Interconnection System

English

### Fine Pitch Stacking Connectors - 0.635mm MICTOR Connectors

English

## Product Specifications

### Application Specification

English