



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**
PCB Mount Orientation: **Vertical**
Connector System: **Board-to-Board**
Number of Positions: **152**
Centerline (Pitch): **.64 mm, 24 mm [.945 in]**

Features

Product Type Features

Ground Component Type	Ground Bus
PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Power Positions	4
Number of Columns	76
Stackable	Yes
Number of Signal Positions	152
PCB Mount Orientation	Vertical
Number of Positions	152
Board-to-Board Configuration	Parallel

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	500 VAC
Insulation Resistance	2 MΩ
Impedance	50 Ω
Operating Voltage	30 VAC

Signal Characteristics



Differential Signaling	Yes
Data Rate	10 Gb/s

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Layout	Inline
Contact Mating Area Length	.94 mm[.037 in]
PCB Contact Termination Area Plating Material Thickness	3.81 – 6.35 µm[149.9997 – 249.9995 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Shape & Form	Dual Beam
Contact Mating Area Plating Material Finish	Matte
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.76 µm[29.9212 µin]
Contact Type	Pin
Contact Current Rating (Max)	11.5 A

Termination Features

Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Rectangular Termination Post & Tail Width	.53 mm[.021 in]
Termination Method to Printed Circuit Board	Surface Mount

Mechanical Attachment

PCB Mount Alignment Type	Positioning Bosses
Mating Retention	With
Mating Alignment	Without
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount

Housing Features

Mating Entry Location	Top
Centerline (Pitch)	.64 mm, 24 mm[.945 in]
Housing Material	Matte



Dimensions

Connector Length	63.45 mm[2.498 in]
Connector Height	6.38 mm[.251 in]
Connector Width	5.28 mm[.208 in]
Stack Height	6.6 mm, 15.62 mm[.615 in]
PCB Thickness (Recommended)	1.57 mm[.8 in]

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Rating	Listed
Agency/Standard	CSA, UL
Approved Standards	CSA 1195944, UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	248
Packaging Type	Reel

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2-5767004-5 MICTOR RECEPT ASSY, 152 POS.	 TE Part # 5767130-4 MICT,RCPT,152,ASY,GOLD,EXTD	 TE Part # 1-5767096-1 MICT,REC,152,ASY,.025,TAPE,CAP	 TE Part # 1-5767114-1 MICT,REC,152,ASY,.025,TAPE PKG
 TE Part # 1-5767115-1 MICT,REC,152,ASY,.025 TAPE PKG	 TE Part # 1-5767145-1 MICTOR RECEPTACLE ASSY, .355 V	 TE Part # 1-5767146-1 TAPE AND REEL PACKAGED RECEPTA	 TE Part # 1-5767153-1 152 POS. .355 VERTICAL RECEPTA
 TE Part # 5767044-4 MICTOR,R/A,RECPT,.062,152,ASY	 TE Part # 5767054-4 MICT,RECPT,152,ASSY,PDNI	 TE Part # 5767061-4 MICT,RECPT,152,ASSY,093,PDNI	 TE Part # 5767081-4 MICT,REC,152,ASY,PDNI,BARBLESS
 TE Part # 5767089-4 MICTOR,R/A,RECPT,.093,152,ASY	 TE Part # 5767094-4 MICT,RECPT,152,ASY,PDNI,EXTD	 TE Part # 5767095-4 MICT,REC,EXT,152,ASY,PDNI,025	 TE Part # 5767096-4 MICT,REC,152,ASY,.025,TAPE PKG



TE Part # 5767110-4
[MICT,RECPT,152,ASSY,.025](#)



TE Part # 5767114-4
[MICT,REC,152,ASY,.025,TAPE,CAP](#)



TE Part # 5767115-4
[MICT,REC,152,ASY,.025 TAPE PKG](#)



TE Part # 5767143-4
[MICT,R/A,RCPT,152,ASY,062,30AU](#)

Documents

Product Drawings

[MICT,PLG,152,ASY,.025,TAPE CAP](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_5767118-4_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5767118-4_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5767118-4_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[MICTOR Interconnection System](#)

English

[Fine Pitch Stacking Connectors Catalog 889092](#)

English

[Fine Pitch Stacking Connectors - 0.635mm MICTOR Connectors](#)

English

Product Specifications

[Application Specification](#)

English