

58075-1 ✓ ACTIVE

AMP

TE Internal #: 58075-1

Hand Crimping Tools, Operator Releasable & Adjustable,  
Pneumatic, Handle Assembly

[View on TE.com >](#)



Application Tooling > Hand Crimping Tools



Ratchet Configuration: **Operator Releasable & Adjustable**

TE Certification: **Cannot be Certified**

Power Technology Type: **Pneumatic**

Tooling Type: **Handle Assembly**

## Features

### Other

Ratchet Configuration	Operator Releasable & Adjustable
TE Certification	Cannot be Certified
Power Technology Type	Pneumatic
Tooling Type	Handle Assembly

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




TE Part # 177534-3  
2.5 M.I.S REC ASSY 3P BLACK



TE Part # 58246-3  
MTA 100 CRIMP HEAD PRODUCTION RBBN CABLE



TE Part # 58247-3  
MTA 156 CRIMP HEAD PRODUCTION RBBN CABLE



TE Part # 177534-4  
2.5 M.I.S REC ASSY 4P BLACK



TE Part # 58246-2  
MTA 100 CRIMP HEAD PRODUCTION DISCRETE



TE Part # 58247-2  
MTA 156 CRIMP HEAD PRODUCTION DISCRETE



TE Part # 2326300-1  
MTE HEAD ASSY, 2MM IDC

TE Part # 173983-2  
AMP CT MT AMP-IN HDR-H NAT 2P

TE Part # 173983-3  
AMP CT MT AMP-IN HDR-H NAT 2P

TE Part # 173983-4  
AMP CT MT AMP-IN HDR-H NAT 4P

TE Part # 173983-5  
AMP CT MT AMP-IN HDR-H NAT 5P




TE Part # 173983-6  
AMP CT MT AMP-IN HDR-H NAT 6P

TE Part # 173983-7  
AMP CT MT AMP-IN HDR-H NAT 7P

TE Part # 173983-8  
AMP CT MT AMP-IN HDR-H NAT 8P

TE Part # 173983-9  
AMP CT MT AMP-IN HDR-H NAT 9P

TE Part # 173985-2  
AMP CT MT AMP-IN HDR-V NAT 2P



## Documents

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_58075-1\\_F.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_58075-1\\_F.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_58075-1\\_F.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### MTA Portable Tooling Solutions

English

#### AMPLIMITE Subminiature D Connectors - Cable Connectors

English

#### Bottoming Dies

English

#### AMPMODU MTE INTERCONNECT SYSTEM

English

### Instruction Sheets

#### Instruction Sheet (U.S.)

English