




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Contacts



Contact Type: **Socket**
Connector System: **Wire-to-Board**
Wire Size: **.05 – .09 mm²**

Features

Product Type Features

Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

Termination Resistance	12 mΩ
Insulation Resistance	5000 MΩ
Dielectric Withstanding Voltage (Max)	750 V
Operating Voltage	250 VAC

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
	100 μin
Wire Contact Termination Area Plating Material	Tin
Contact Shape & Form	Square
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Type	Socket
Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Accepts Wire Insulation Diameter Range	.74 – .99 mm[.029 – .039 in]
Wire Size	.05 – .09 mm²

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Approved Standards	UL E28476
--------------------	-----------

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Other

Comment	(*) For use with Model "K" machines. Call the Technical Assistance Center (1-800-522-6752) for any tooling questions., These contacts must be crimped per AMP Specification No. 114-25006 in order to function properly in a connector housing.
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>







EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 87175-2 01 LOCKING CLIP HSG SR .100CL	 TE Part # 87133-1 04 LOCKING CLIP HSG DR .100CL	 TE Part # 926657-6 LOCKING CLIP HSG	 TE Part # 926657-4 LOCKING CLIP HSG
 TE Part # 1-87175-0 04 LOCKING CLIP HSG SR .100CL	 TE Part # 926209-3 LOCKING CLIP HSG.	 TE Part # 1-87175-7 08 LOCKING CLIP HSG SR MRKD	 TE Part # 87133-9 08 LOCKING CLIP HSG DR .100CL
 TE Part # 926010-1 LOCKING CLIP HSG	 TE Part # 1-87175-2 05 LOCKING CLIP HSG SR .100CL	 TE Part # 87133-2 10 LOCKING CLIP HSG DR .100CL	 TE Part # 926209-5 LOCKING CLIP HSG.



 TE Part # 1-87133-1 12 LOCKING CLIP HSG DR .100CL	 TE Part # 1-87175-3 06 LOCKING CLIP HSG SR MRKD	 TE Part # 1-87175-4 06 LOCKING CLIP HSG SR .100CL	 TE Part # 1-87175-6 07 LOCKING CLIP HSG SR .100CL
 TE Part # 1-87175-8 08 LOCKING CLIP HSG SR .100CL	 TE Part # 2-87175-2 10 LOCKING CLIP HSG SR .100CL	 TE Part # 926209-4 2X4P LOCK-CLIP GEH	 TE Part # 2-87175-8 13 LOCKING CLIP HSG SR .100CL

Documents

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_5-87191-2_J.3d_igs.zip

English

Customer View Model

ENG_CVM_5-87191-2_J.3d_stp.zip

English

Customer View Model

ENG_CVM_5-87191-2_J.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION5_CONT

English

Product Specifications

Application Specification

English