




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 2.08 mm²**

Mating Tab Width: **5.21 mm [ .205 in ]**

Mating Tab Thickness: **.81 mm [ .032 in ]**

Features

Product Type Features

|                 |              |
|-----------------|--------------|
| Terminates To   | Wire & Cable |
| Wire/Cable Type | Regular Wire |
| Wire Stop       | No           |
| Insertion Force | Low          |
| Sealable        | No           |

Configuration Features

|                     |        |
|---------------------|--------|
| Connection Capacity | Single |
|---------------------|--------|

Contact Features

|                                |                  |
|--------------------------------|------------------|
| Quick Disconnect Terminal Type | Receptacle       |
| Mating Tab Width               | 5.21 mm[.205 in] |
| Mating Tab Thickness           | .81 mm[.032 in]  |
| Terminal Orientation           | Flag             |
| Contact Base Material          | Brass            |
| Terminal Plating Material      | Tin              |
| Crimp Type                     | Tab-Lok          |



|             |      |
|-------------|------|
| Barrel Type | Open |
|-------------|------|

Mechanical Attachment

|                         |         |
|-------------------------|---------|
| Mating Retention Type   | Dimple  |
|                         | .035 in |
| Wire Insulation Support | With    |

Dimensions

|                                        |                              |
|----------------------------------------|------------------------------|
| Accepts Wire Insulation Diameter Range | 2.79 – 4.32 mm[.11 – .17 in] |
| Receptacle Terminal Stock Thickness    | .41 mm[.016 in]              |
| Overall Length                         | 13.46 mm[.53 in]             |
| Wire Size                              | .51 – 2.08 mm²               |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Insulation Option           | Uninsulated                |
| Operating Temperature Range | -40 – 110 °C[-40 – 230 °F] |

Industry Standards

|               |        |
|---------------|--------|
| CSA Certified | Yes    |
| UL Rating     | Listed |

Packaging Features

|                    |            |
|--------------------|------------|
| Packaging Quantity | 5000       |
| Packaging Method   | Strip/Reel |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JUNE 2022 (224)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                    |



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 565501-1  
STD HBEMPR140T140OK

Also in the Series | FASTON 205

Crimp Terminal Housings(3)

PCB Terminals(9)

Quick Disconnects(36)

Documents

Product Drawings  
205 FASTON FLAG REC 20-14 AWG TPBR  
English

CAD Files  
Customer View Model  
ENG\_CVM\_CVM\_60195-2\_T.2d\_dxf.zip  
English

3D PDF  
3D  
Customer View Model



[ENG\\_CVM\\_CVM\\_60195-2\\_T.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_60195-2\\_T.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[82004 FASTON Terminals \(Insulated and Uninsulated\) Catalog - FASTON Receptacles Section](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English