




**AMPLIMITE**

TE Internal #: 5-1478763-3

D-Sub Backshells & Clamps, Backshell Kit, Two-Piece RFI/EMI Shield, Split-Ring, Cable-to-Panel / Cable-to-Cable, 25 Position, Size 3, Shielded

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: **Backshell Kit**

Cable Clamp Type: **Two-Piece RFI/EMI Shield**

Ferrule Type: **Split-Ring**

Connector System: **Cable-to-Cable, Cable-to-Panel**

Number of Positions: **25**

**Features**

**Product Type Features**

D-Shaped Connector Accessories	Backshell Kit
Connector System	Cable-to-Cable, Cable-to-Panel
Connector & Contact Terminates To	Wire & Cable

**Configuration Features**

Number of Positions	25
---------------------	----

**Body Features**

Cable Clamp Type	Two-Piece RFI/EMI Shield
Ferrule Type	Split-Ring
Cable Exit Angle	45°

**Mechanical Attachment**

Connector Mounting Type	Cable Mount (Free-Hanging), Panel Mount
-------------------------	---

**Usage Conditions**

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

## Operation/Application

Compatible With Connector Shell Size	3
Shielded	Yes

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Documents



### Product Drawings

[Metal backshell 25 way 45 Deg Entry-KIT](#)

English

[Metal backshell 25 way 45 Deg Entry-KIT](#)

English

---

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_5-1478763-3\\_G.2d\\_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_5-1478763-3\\_G.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5-1478763-3\\_G.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Specifications

[Application Specification](#)

English