



**RAYCHEM**

TE Internal #: 650027-000

Splices, Sealable, 0 Serration, Length 40.2 mm [1.58 in], Bag/Box, Discrete Wire, Fully Insulated, Non-Insulation Support, -55 – 150 °C [-67 – 302 °F]

[View on TE.com >](#)

Terminals & Splices > Splices



Sealable: **Yes**

Serrated: **No**

Number of Serrations: **0**

Overall Product Length: **40.2 mm [ 1.58 in ]**

Government Qualified Splice: **No**

**Features**

**Product Type Features**

Sealable	Yes
Serrated	No
Wire Insulation Support Retention Type	Non-Insulation Support

**Configuration Features**

Number of Serrations	0
Compatible With Wire & Cable Type	Discrete Wire

**Body Features**

Insulation Material	Modified Polyvinylidene
---------------------	-------------------------

**Dimensions**

Overall Product Length	40.2 mm[1.58 in]
------------------------	------------------

**Usage Conditions**

Insulation Option	Fully Insulated
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]

**Operation/Application**

Heavy Duty	No
------------	----

**Industry Standards**

Government Qualified Splice	No
-----------------------------	----

## Packaging Features

Packaging Method

Bag/Box

## Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)  
Candidate List Declared Against: JAN 2022 (223)  
Does not contain REACH SVHC

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 992008-000  
[AD-1377-CRIMP-TOOL-3-CVTY](#)

## Documents

### Product Drawings



[D-436-73](#)

English

---

[Datasheets & Catalog Pages](#)

[1654025\\_Sec8\\_D-436](#)

English

[Harness Repair Products Quick Reference Guide](#)

English