

6009114013 ✓ ACTIVE

RAYCHEM | RAYCHEM DWP-125

TE Internal #: 6009114013

Heat Shrink Tubing, Black, Dual Wall, .126 in [3.2 mm] Expanded Inside, .039 in [1 mm] Recovered Inside, 3:1 Shrink Ratio, RAYCHEM DWP-125

[View on TE.com >](#)



Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Dual**

Expanded Inside Diameter (Min): **3.2 mm [.126 in]**

Recovered Inside Diameter (Max): **1 mm [.039 in]**

Shrink Ratio: **3:1**

Features

Product Type Features

| | |
|-----------|------|
| Wall Type | Dual |
|-----------|------|

Body Features

| | |
|--------------------------|--|
| Fluid Type | Brake Fluid, Hydraulic Fluid, Lubricating Oil, Water |
| Primary Product Color | Black |
| Shrink Ratio | 3:1 |
| Primary Product Material | Irradiated Modified Polyolefin |
| Flexibility | Flexible |

Dimensions

| | |
|------------------------------------|----------------------------|
| Recovered Wall Thickness (Nominal) | 1.02 mm[.04 in] |
| Expanded Inside Diameter (Min) | 3.2 mm[.126 in] |
| Recovered Inside Diameter (Max) | 1 mm[.039 in] |
| Heat Shrink Tubing Size Range | 1 – 3.2 mm[.039 – .126 in] |

Usage Conditions

| | |
|---------------------------------|-------------------|
| Shrink Temperature (Min) | 80 °C |
| Fluid Resistance | Splash Protection |
| Heat Shrink Tubing Flammability | Flame-Retardant |
| Operating Temperature Range | -40 – 110 °C |



| | |
|-------------------------------|---------------------------|
| Heat Shrink Tubing Resistance | Fluids, Mechanical Damage |
|-------------------------------|---------------------------|

| | |
|----------------------|--------|
| Recovery Temperature | 125 °C |
|----------------------|--------|

Product Availability

| | |
|-------------------|--------|
| Applicable Region | Global |
|-------------------|--------|

Packaging Features

| | |
|------------------|-------|
| Packaging Method | Spool |
|------------------|-------|

Other

| | |
|-----------------------------------|----|
| Meets Low Outgassing Requirements | No |
|-----------------------------------|----|

| | |
|----------------|----------------|
| Product Source | Czech Republic |
|----------------|----------------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
|------------------------------|-----------|

| | |
|-----------------------------|-----------|
| EU ELV Directive 2000/53/EC | Compliant |
|-----------------------------|-----------|

| | |
|---|---|
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
|---|---|

| | |
|--|---|
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
|--|---|

| | |
|-----------------|--|
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
|-----------------|--|

| | |
|---------------------------|--|
| Solder Process Capability | Not applicable for solder process capability |
|---------------------------|--|

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CJ2087-000
HL2010E-KIT-120V



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | [RAYCHEM DWP-125](#)



[Heat Shrink Tubing\(119\)](#)

Documents

Product Drawings

[DWP-125-3/16-0-SP](#)

English

Datasheets & Catalog Pages

[Flexible, Flame-Retardant, Adhesive-lined, Polyolefin Heat-Shrinkable Tubing](#)

English

[Measuring_Single_Wall_Tubing](#)

English

[Selecting_Correct_Tubing](#)

English

Product Specifications

[Quality Specification](#)

English