




Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**
Operating Voltage: **250 VAC**
Contact Mating Area Plating Material: **Tin**
Wire Size: **.2 – .82 mm²**

Features

Product Type Features

Power Contact Type	Contact
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Contact Shape & Form	Round
Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	15 A
Contact Type	Socket
Contact Retention Within Housing	With
Mating Pin Diameter	2.13 mm[.084 in]
Contact Base Material	Phosphor Bronze
Wire Contact Termination Area Plating Material	Tin
Wire Contact Termination Area Plating Material Finish	Bright



Contact Orientation	Straight
Barrel Type	Open Barrel

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
Connector Mounting Type	Cable Mount (Free-Hanging)
Wire Insulation Support	Without

Dimensions

Wire Size	.2 – .82 mm²
Accepts Wire Insulation Diameter Range	2.54 mm[.1 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
VDE Tested	No

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Other

Wire/Cable Type	Discrete Wire
Wire Type	Stranded
For Use With	Commercial MATE-N-LOK housings

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)
Candidate List Declared Against: JUNE 2022 (224)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 91512-1
CCII CMNL PIN SKT 24-18 ASSY

TE Part # 90574-1
ASSY PRO-CRIMPER COMM M-N-LOCK

TE Part # 465644-1
EXTRACTION TOOL

TE Part # 455830-1
INSERTION TOOL

TE Part # 1-171196-0
6 POS MATE-N-LOK S

TE Part # 1-480274-0
09P CMNL PLUG HSG P/M NATL


TE Part # 1-480284-0
08P CMNL CAP HSG M/M NATL

TE Part # 1-480438-0
16P CMNL PLUG HSG M/M NATL



 TE Part # 1-480683-0 02P CMNL PLUG HSG F/H NATL	 TE Part # 1-480277-0 09P CMNL CAP HSG P/M NATL	 TE Part # 1-480304-0 03P CMNL PLUG HSG P/M NATL	 TE Part # 1-480722-0 04P CMNL PLUG HSG W/LCK NATL
 TE Part # 1-480276-0 06P CMNL CAP HSG P/M NATL	 TE Part # 1-480285-0 10P CMNL PLUG HSG M/M NATL	 TE Part # 1-480439-0 16P CMNL CAP HSG M/M NATL	 TE Part # 1-480393-1 02P CMNL PLUG HSG F/H BLK
 TE Part # 1-480345-0 08P CMNL CAP HSG F/H NATL	 TE Part # 1-480340-0 06P CMNL CAP HSG F/H NATL	 TE Part # 1-480278-0 12P CMNL CAP HSG P/M NATL	 TE Part # 1-480425-0 04P CMNL PLUG HSG P/M NATL

Also in the Series | Commercial MATE-N-LOK

 Connector Contacts(26)	 Crimp Wire Pins, Tabs & Ferrules(3)	 Insertion & Extraction Tools(5)	 Power Contacts(129)
 Rectangular Caps & Covers(2)	 Rectangular Connector Housings(17)	 Rectangular Connector Seals(1)	 Rectangular Power Connectors(170)



Standard Circular Connectors(4)



Standard Rectangular Connectors(10)



Wire-to-Board Connector Contacts(1)

Documents

Product Drawings

CMNL SOK PTPPHBZ L/P

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_60617-4_V.2d_dxf.zip

English

Customer View Model

ENG_CVM_60617-4_V.3d_igs.zip

English

Customer View Model

ENG_CVM_60617-4_V.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_60617-4_Z.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_60617-4_Z.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_60617-4_Z.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

Product Specifications

Application Specification



English

Product Environmental Compliance

MD_60617-4_042220142145_dmtec

English

MD_60617-4_042220142145_dmtec

English

Instruction Sheets

Instruction Sheet (U.S.)

English