



RAYCHEM

TE Internal #: 674339-000

Rectangular Contact Inserts, Socket, Socket, Wire-to-Wire, 5 Position, .05 in [1.27 mm] Centerline, Sealable, Wire & Cable, 16 AWG Wire Size

[View on TE.com >](#)

Connectors > Rectangular Connectors > Rectangular Contact Inserts



Rectangular Connector Insert Type: **Socket**

Contact Type: **Socket**

Connector System: **Wire-to-Wire**

Number of Positions: **5**

Centerline (Pitch): **1.27 mm [.05 in]**

Features

Product Type Features

Product Type	Contact Insert
Shell Size	50.8 [2]
Rectangular Connector Insert Type	Socket
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Keying	A/B
Number of Positions	5

Body Features

Material	High Grade Polyarylene Thermoplastic
Rear Grommet	With
Module Material	High Grade Polyarylene Thermoplastic
Interfacial Seal	Without
Insert Type	Environmental
Color	Black

Contact Features

Contact Type	Socket
--------------	--------



Contact Current Rating (Max)	1.5 A
------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Panel Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	1.27 mm[.05 in]
--------------------	-----------------

Dimensions

Accepts Wire Insulation Diameter Range	1.65 – 2.77 mm[.065 – .109 in]
--	--------------------------------

Wire Size	1.5 mm ²
-----------	---------------------

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JUNE 2022 (224)</p> <p>Candidate List Declared Against: JAN 2022 (223)</p> <p>SVHC > Threshold:</p> <p>Octamethylcyclotetrasiloxane (D4) (1% in COMPONENT)</p>
--	---

Article Safe Usage Statements:
Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.


Halogen Content	Not Yet Reviewed for halogen content
-----------------	--------------------------------------

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

[MTCP-116-05S2](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_674339-000_C_c-674339-000-c.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_674339-000_C_c-674339-000-c.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_674339-000_C_c-674339-000-c.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Products for Aerospace and Defense](#)

English

Product Specifications

[MTC Quick-Disconnect Connectors with Removable Contacts](#)

English

[MTC Connectors with Removable Contacts and Jackscrew Coupling Hardware](#)

English

[Assembly Procedures for MTCP and MTCR Connectors AWIP Program](#)

English