




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **1.03 – 2.62 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Terminates To	Wire & Cable
Wire/Cable Type	Regular Wire
Wire Stop	No
Insertion Force	Normal
Sealable	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Electrical Characteristics

Voltage (Max)	250 V
---------------	-------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight



Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Mating Retention Type	Locking Lance
Locking Lance Height	.32 mm
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	3.43 – 5.08 mm[.135 – .2 in]
Receptacle Terminal Stock Thickness	.33 mm[.013 in]
Overall Length	19.2 mm[.755 in]
Wire Size	1.03 – 2.62 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	5000
Packaging Method	Strip/Reel

Other

Comment	"According to DIN 46340, Part 3", Chamfered, Without Dimple
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224)





Candidate List Declared Against: JUNE 2022 (224)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-1579007-4 EXTRACTION TOOL	 TE Part # 4-1579007-3 EXTRACTION TOOL KIT	 TE Part # 1989880-1 .250 SRS FASTIN-ON REC.	 TE Part # 626328-2 FF 250 RECEPTACLE 4.0-6.0 MM2 TPBR
 TE Part # 160950-1 FF 250 REC BR SOLDERING	 TE Part # 2-2150314-1 OCEAN_2.0_Applicator-E-110F180F	 TE Part # 2-2150314-2 OCEAN_2.0_Applicator-E-110F180FA	 TE Part # 2-2150427-1 OCEAN_2.0_APPLICATOR-E-110F140OV



TE Part # 2-2150427-2 OCEAN_2.0_APPLICATOR-E-110F140OVA	TE Part # 2150314-1 OCEAN_2.0_Applicator-E-110F180F	TE Part # 2150314-2 OCEAN_2.0_Applicator-E-110F180FA	TE Part # 2150427-1 OCEAN_2.0_APPLICATOR-E-110F140OV
TE Part # 2150427-2 OCEAN_2.0_APPLICATOR-E-110F140OVA	TE Part # 626096-2 .250 S FASTIN ON	TE Part # 626328-1 FF 250 RECEPTACLE 4.0-6.0 MM2 BR	TE Part # 7-2150314-1 OCEAN_2.0_Applicator-E-110F180F
TE Part # 7-2150314-2 OCEAN_2.0_Applicator-E-110F180FA	TE Part # 7-2150314-7 OCEAN_2.0_SPARE_PART_KIT-110F180F	TE Part # 7-2150427-1 OCEAN_2.0_APPLICATOR-E-110F140OV	TE Part # 7-2150427-2 OCEAN_2.0_APPLICATOR-E-110F140OVA

Also in the Series | FASTIN-FASTON 250

Crimp Terminal Housings(218)	Insertion & Extraction Tools(2)	PCB Terminals(2)	Quick Disconnects(255)
-------------------------------------	--	-------------------------	-------------------------------

Documents

Product Drawings
FF 250 REC 1.0-2.5MM2 TPBR
English

CAD Files
3D PDF
3D
Customer View Model



[ENG_CVM_CVM_6-160448-5_AR_c-6-160448-5-ar.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-160448-5_AR_c-6-160448-5-ar.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-160448-5_AR_c-6-160448-5-ar.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

Product Specifications

[EB**General Application Specification for Open Barrel Terminals](#)

English

[Application Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English