

6-786862-5 ✓ ACTIVE

AMPLIMITE | AMPLIMITE 0.50 Series

TE Internal #: 6-786862-5

IDC D-Sub Connectors, Receptacle, 30 – 28 AWG Solid Wire Size, .

05 – .1 mm<sup>2</sup> Solid Wire Size, Cable-to-Panel, 50 Position,

AMPLIMITE 0.50 Series

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors > IDC D-Sub: Receptacle Kit, Panel Mount, Signal, 1.27 mm



Connector & Housing Type: **Receptacle**

Solid Wire Size: **.05 – .1 mm<sup>2</sup>**

Shielded: **No**

Connector System: **Cable-to-Panel**

[All IDC D-Sub: Receptacle Kit, Panel Mount, Signal, 1.27 mm \(7\)](#)

## Features

### Product Type Features

Rails	Without
Connector & Housing Type	Receptacle
Connector System	Cable-to-Panel
Connector Product Type	Connector Kit
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	50
Number of Rows	2
Compatible With Wire & Cable Type	Flat Ribbon Cable, Round Jacketed Cable

### Body Features

Bracket Material	Zinc
Color	Black
Bracket Plating Material	Nickel over Copper
Cover Material	Polyester
Ribbon Cable Centerline Spacing	.64 mm[.025 in]
Shell Material	Carbon Steel
Shell Plating Material	Nickel over Copper

### Contact Features

	30 µin
Contact Mating Area Plating Material	Gold or Gold Flash over Palladium Nickel
Contact Underplating Material	Nickel, Palladium Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	1 A

### Termination Features

Termination Cover Type	Standard
Termination Cover Method	Assembled
Termination Cover	With
Termination Method to Wire & Cable	Insulation Displacement (IDC)

### Mechanical Attachment

Mating Connector Lock	With
Mounting Angle	None
Mating Connector Lock Type	Latch Blocks
Panel Mount Feature	With
PCB Mount Retention Type	None
Detent	Without
Screw & Hole Thread Size	2-56 UNC
Connector Mounting Type	Panel Mount

### Housing Features

Housing Material	Polyester
Housing Color	Black
Centerline (Pitch)	1.27 mm[.05 in]

### Dimensions

Insulation Diameter (Max)	.79 mm
Accepts Wire Insulation Diameter Range	.74 – .79 mm[.029 – .031 in]
Solid Wire Size	.05 – .1 mm <sup>2</sup>
Wire Size	.05 – .09 mm <sup>2</sup>

### Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------



### Operation/Application

Shielded	No
Circuit Application	Signal

### Industry Standards

UL Flammability Rating	UL 94V-0
Cover Flammability Rating	UL 94V-0

### Packaging Features

Packaging Method	Kit
Packaging Quantity	10

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: DEC 2012 (138) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



TE Part # 5749111-4  
50 50SR CABLE PLUG ASSY



TE Part # 5749699-5  
50 50SR CABLE RCPT KIT



TE Part # CAT-AM7-22507  
IDC D-Sub: Connector Kit, Plug, Signal, 1.27 mm



TE Part # 5749193-1  
50 50SR KIT,ST,UK



TE Part # 5749080-1  
50 50SR BSHLL KIT,M/J-SCR



TE Part # 5749193-2  
50 50SR KIT,ST,UK



TE Part # 5749889-3  
50 50SR KIT,ST,UK



TE Part # 5390377-5  
50 POS A/P PLUG 25 CL 30AU



TE Part # 5749210-5  
50 50SR CABLE RCPT ASSY



TE Part # 786585-3  
50SR SCREWLOCK KIT,BULK,FEMAL



TE Part # 786585-2  
50SR SCREWLOCK KIT,FEMALE



TE Part # 749087-1  
50SR SCREWLOCK KIT,FEMALE



TE Part # 749087-2  
50SR SCREWLOCK KIT,FEMALE



TE Part # 749087-4  
50SR SCREWLOCK KIT,FEMALE




TE Part # 749087-3  
50SR SCREWLOCK KIT,FEMALE



TE Part # 5-749611-5  
50 50SR PANEL MOUNT RCPT, ROHS


## Also in the Series | AMPLIMITE 0.50 Series



D-Sub Backshells & Clamps(31)



D-Sub Covers(20)



D-Sub Locking & Mounting(8)



IDC D-Sub Connectors(76)



Insertion & Extraction Tools(1)



PCB D-Sub Connectors(191)

## Documents

### Product Drawings

[50 50SR PANEL MOUNT RCPT S/A, ROHS](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_6-786862-5\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_6-786862-5\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_6-786862-5\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - .050 Series Connector](#)

English

[AMPLIMITE .050 Series D-sub Connectors QRG](#)

English

### Product Specifications

[Application Specification](#)

English

### Agency Approvals

[UL](#)

English