




MULTI-BEAM

TE Internal #: 6600122-9  
Rectangular Power Connectors, Header, Plug, Board-to-Board, 32  
Position, 5.08 mm / 5.71 mm / 2.54 mm [.225 in / .2 in / .1 in]  
Centerline  
[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**  
Connector & Housing Type: **Plug**  
Connector System: **Board-to-Board**  
Number of Positions: **32**  
Centerline (Pitch): **2.54 mm, 5.08 mm, 5.71 mm [ .1 in, .2 in, .225 in ]**

Features

Product Type Features

|                                   |                       |
|-----------------------------------|-----------------------|
| Header Type                       | Fully Shrouded        |
| Rectangular Power Connector Type  | Header                |
| Connector & Housing Type          | Plug                  |
| Connector System                  | Board-to-Board        |
| Sealable                          | No                    |
| Connector & Contact Terminates To | Printed Circuit Board |

Configuration Features

|                            |             |
|----------------------------|-------------|
| Number of Positions        | 32          |
| PCB Mount Orientation      | Right Angle |
| Number of Power Positions  | 88          |
| Number of Signal Positions | 24          |

Electrical Characteristics

|                   |        |
|-------------------|--------|
| Operating Voltage | 60 VDC |
|-------------------|--------|

Contact Features

|                                                |                                  |
|------------------------------------------------|----------------------------------|
| Contact Underplating Material                  | Nickel                           |
| Contact Current Rating (Max)                   | 42 A                             |
| Contact Retention Within Housing               | Without                          |
| Contact Type                                   | Blade, Pin                       |
| PCB Contact Termination Area Plating Material  | Tin                              |
| Contact Mating Area Plating Material           | Gold Flash over Palladium Nickel |
| Contact Mating Area Plating Material Thickness | .76 µm[30 µin]                   |

Termination Features

|                                             |                       |
|---------------------------------------------|-----------------------|
| Termination Method to Printed Circuit Board | Through Hole - Solder |
|---------------------------------------------|-----------------------|

Mechanical Attachment

|                         |             |
|-------------------------|-------------|
| Connector Mounting Type | Board Mount |
|-------------------------|-------------|

Housing Features

|                    |                                                  |
|--------------------|--------------------------------------------------|
| Centerline (Pitch) | 2.54 mm, 5.08 mm, 5.71 mm[.1 in][.2 in][.225 in] |
| Housing Color      | Black                                            |
| Housing Material   | High Temperature Thermoplastic                   |

Usage Conditions

|                             |                           |
|-----------------------------|---------------------------|
| Operating Temperature Range | -20 – 105 °C[-4 – 221 °F] |
|-----------------------------|---------------------------|

Operation/Application

|                     |                |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

Industry Standards

|                        |                                       |
|------------------------|---------------------------------------|
| UL Flammability Rating | UL 94V-0                              |
| Glow Wire Rating       | High Temperature Part - Not Glow Wire |

Packaging Features

|                  |      |
|------------------|------|
| Packaging Method | Tray |
|------------------|------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                         |
|-----------------------------------------------|-----------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                               |
| EU ELV Directive 2000/53/EC                   | Compliant                               |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006        |                                         |



Current ECHA Candidate List: JUNE 2022 (224)  
Candidate List Declared Against: JUNE 2022 (224)  
Does not contain REACH SVHC


|                 |                                                |
|-----------------|------------------------------------------------|
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
|-----------------|------------------------------------------------|

|                           |                              |
|---------------------------|------------------------------|
| Solder Process Capability | Wave solder capable to 265°C |
|---------------------------|------------------------------|

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6450830-1  
MBXL R/A HDR 2LP + 8S + 2LP

Documents

Product Drawings  
MBXL R/A HDR DB 24S+8P  
English

CAD Files  
Customer View Model  
ENG\_CVM\_CVM\_6600122-9\_D.2d\_dxf.zip  
English  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_6600122-9\_D.3d\_igs.zip  
English



Customer View Model

[ENG\\_CVM\\_CVM\\_6600122-9\\_D.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[2\\_PIECE\\_POWER\\_CONNECTORS\\_qrg\\_4-1773458-1](#)

English

Product Specifications

[Application Specification](#)

English