

745207-7 ✓ ACTIVE

AMPLIMITE | AMPLIMITE HDE


TE Internal #: 745207-7

IDC D-Sub Connectors, Plug, 26 – 22 AWG Solid Wire Size, Wire-to-Wire, 15 Position, 2.77 mm [.055 in] Centerline, 2 Row, AMPLIMITE HDE

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors > IDC D-Sub: Plug Assembly, Wire to Wire, Signal, 2.77 mm



Connector & Housing Type: **Plug**

Solid Wire Size: **26 – 22 AWG**

Shielded: **No**

Connector System: **Wire-to-Wire**

Number of Positions: **15**

[All IDC D-Sub: Plug Assembly, Wire to Wire, Signal, 2.77 mm \(21\)](#)

## Features

### Product Type Features

Grade	Standard
Grounding Indents	Without
Shell Type	All Plastic
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Connector Product Type	Connector Assembly
D-Sub Shell Size	2
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	15
Number of Rows	2
Compatible With Wire & Cable Type	Discrete Wire, Round Jacketed Cable



### Body Features

Color	Black
-------	-------

### Contact Features

PCB Termination Area Plating Finish	Matte
Contact Type	Pin
	30 $\mu$ m
D-Sub Contact Size	20
Contact Current Rating (Max)	2.4 A

### Mechanical Attachment

Mating Connector Lock	With
Mounting Angle	Straight
Mating Connector Lock Type	Mounting Holes
Connector Mounting Type	Cable Mount (Free-Hanging)

### Housing Features

Housing Material	Thermoplastic
Enclosure	Without
Centerline (Pitch)	2.77 mm [.055 in]

### Dimensions

Solid Wire Size	26 – 22 AWG
Wire Size	.15 – .4 mm <sup>2</sup>

### Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

### Operation/Application

Shielded	No
Circuit Application	Signal

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Method	Package
Packaging Quantity	112

### Other

--	--



Comment	HDE connectors are designed for terminating solid or stranded (7-strand max.) wire.
---------	---

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts

 <p>TE Part # CAT-025-DRAVS2274 D-Sub Receptacle Assembly: Vertical, Shell Size 2, 2.74mm</p>	 <p>TE Part # CAT-023-DRARS2274 D-Sub Receptacle Assembly: Right Angle, Shell Size 2, 2.74mm</p>	 <p>TE Part # 745205-7 15 HDE AP RECEPT, LEAD FREE</p>	 <p>TE Part # CAT-AM7-253 IDC D-Sub: Receptacle Assembly, Low Profile, Signal, 2.77 mm</p>
--	--	---	---



## Also in the Series | AMPLIMITE HDE



## Documents

### Product Drawings

#### 15 HDE AP PLUG, LEAD FREE

English

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_745207-7\\_M.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_745207-7\\_M.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_745207-7\\_M.3d\\_stp.zip](#)

English

### 3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### AMPLIMITE Subminiature D Connectors - Cable Connectors

English

#### AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

### Product Specifications



### Application Specification

English

---

### Product Environmental Compliance

#### TE Material Declaration

English

---

### Instruction Sheets

#### Instruction Sheet (U.S.)

English

---

### Agency Approvals

#### UL Report

English