

747547-9 ✓ ACTIVE

AMPLIMITE | AMPLIMITE HDE

TE Internal #: 747547-9

IDC D-Sub Connectors, Plug, 26 – 22 AWG Solid Wire Size, .13 – .32 mm<sup>2</sup> Solid Wire Size, Shielded, Cable-to-Cable, 25 Position, AMPLIMITE HDE

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors > IDC D-Sub: Connector Kit, Plug, Wire to Wire, Signal, 2.77 mm



Connector & Housing Type: **Plug**

Solid Wire Size: **.13 – .32 mm<sup>2</sup>**

Shielded: **Yes**

Connector System: **Cable-to-Cable**

[All IDC D-Sub: Connector Kit, Plug, Wire to Wire, Signal, 2.77 mm \(17\)](#)

## Features

### Product Type Features

Grade	Standard
Grounding Indents	With
Shell Type	Front Metal Shell
Connector & Housing Type	Plug
Connector System	Cable-to-Cable
Connector Product Type	Connector Kit
D-Sub Shell Size	3
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Pre-Assembled	No
Number of Positions	25
Number of Rows	2
Compatible With Wire & Cable Type	Discrete Wire, Round Jacketed Cable

### Body Features

Shield Material	Steel
Color	Black
Shell Material	Steel



Insert Material	Thermoplastic
Shell Plating Material	Tin
Shield Plating Material	Tin

### Contact Features

Contact Type	Pin
Contact Mating Area Plating Thickness	.76 μm[30 μin]
Contact Mating Area Plating Material	Gold
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
D-Sub Contact Size	20
Contact Current Rating (Max)	5 A

### Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

### Mechanical Attachment

Mating Connector Lock	With
Mounting Angle	Straight
Mating Connector Lock Type	Mounting Holes
Wire Insulation Support	With
PCB Mount Retention Type	None
Connector Mounting Type	Cable Mount (Free-Hanging)

### Housing Features

Enclosure	With
Centerline (Pitch)	1.38 mm[.054 in]

### Dimensions

Cable Outside Diameter	4.19 – 11.56 mm[.165 – .455 in]
Cable Insulation Diameter Range	4.19 – 11.56 mm[.165 – .455 in]
Accepts Cable Diameter (Max)	11.56 mm[.455 in]
Accepts Wire Insulation Diameter Range	1.52 mm[.06 in]
Solid Wire Size	.13 – .32 mm <sup>2</sup>
Wire Size	.15 – .4 mm <sup>2</sup>

### Usage Conditions



Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

### Operation/Application

Shielded	Yes
Circuit Application	Signal

### Industry Standards

Insert Flammability Rating	UL 94V-0
----------------------------	----------

### Packaging Features

Packaging Method	Package
Packaging Quantity	1

### Other

Comment	Components shipped unassembled, each part bulk-packaged., Maximum cable diameter after jacket and braid removed.
---------	--

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-023-DRARS3277  
D-Sub Receptacle Assembly: Right Angle, Shell Size 3, 2.77mm



TE Part # CAT-025-DRAVS3277  
D-Sub Receptacle Assembly: Vertical, Shell Size 3, 2.77mm



TE Part # CAT-AM7-248H5  
IDC D-Sub: Receptacle Assembly, Wire to Wire, Signal, 2.77 mm



TE Part # CAT-AM7-253  
IDC D-Sub: Receptacle Assembly, Low Profile, Signal, 2.77 mm



TE Part # CAT-026-RAVSAP3277  
D-Sub Receptacle Assembly: Vertical, Action Pin, Shell Size 3, 2.77mm



TE Part # CAT-AM7-248H6  
IDC D-Sub: Receptacle Kit, Wire to Wire, Signal, 2.74 mm



TE Part # 58074-1  
MTA 50/100/156 MANUAL TOOL FRAME



TE Part # 747548-8  
KIT, RCPT, 25P, HDE, SHLD HDWRE



TE Part # 7-1393740-2  
V42254A2216B225=SUB D FEDERLEI



TE Part # 8-1393480-3  
V23529B1223B225=SUB D FEDERLEI



TE Part # 3-1393480-0  
V23529B1122B225=SUB D FEDERLEI



TE Part # 1-1393480-9  
V23529B1121B225=SUB D FEDERLEI



TE Part # 8-1393480-4  
V23529B1223B237=SUB D FEDERLEI



TE Part # 1393481-2  
V23529B1225B225=SUB D FEDERLEI



TE Part # 5-1393480-7  
V23529B1221B225=SUB D FEDERLEI



TE Part # 9-1393480-2  
V23529B1224B225=SUB D FEDERLEI



TE Part # 608868-1  
HDE HT PKG FOR SUB D



TE Part # 7-338315-2  
25POS.HD20 REC.ASSY



TE Part # 8-338315-2  
25P.HDP20 REC.ASSY




TE Part # 9-338315-2  
25POS.HD20 REC.ASSY

Also in the Series | **AMPLIMITE HDE**



Crimp D-Sub Connectors(1)



D-Sub Connector Contacts(13)



IDC D-Sub Connectors(75)



Insertion &amp; Extraction Tools(2)

## Documents

### Product Drawings

[KIT,PLUG,25P,HDE,SHLD HDWRE](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_747547-9\\_J.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_747547-9\\_J.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_747547-9\\_J.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Cable Connectors](#)

English

[AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG](#)

English

### Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English



---

**Agency Approvals**

**UL Report**

English

**UL Report**

English