

749805-9 ✓ ACTIVE

AMPLIMITE


TE Internal #: 749805-9

Crimp D-Sub Connectors, Plug, Cable-to-Cable, 25 Position, Size 20, Size 3, Mating Retention, Shielded

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connectors > Crimp D-Sub Connectors > D-Sub Crimp: Plug, Signal, 25 Posn, Pin Size 20, Shell Size 3



Connector & Housing Type: **Plug**

Connector System: **Cable-to-Cable**

Number of Positions: **25**

D-Sub Contact Size: **20**

D-Sub Shell Size: **3**

[All D-Sub Crimp: Plug, Signal, 25 Posn, Pin Size 20, Shell Size 3 \(9\)](#)

Features

Product Type Features

Grounding Indents	With
Product Type	Connector
Grade	Standard
Grommets	With
Shell Type	Full Metal Shell
Connector & Housing Type	Plug
Connector System	Cable-to-Cable
D-Sub Shell Size	3
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	25
---------------------	----

Body Features



Shell Plating Material	Tin over Copper
Shell Material	Steel
Retainer Clip Material	Stainless Steel
Insert Material	Nylon GF
Contact Features	
D-Sub Contact Size	20
Termination Features	
Termination Method to Wire & Cable	Crimp
Mechanical Attachment	
Mounting Screw Plating Material	Zinc
Mounting Screw Material	Steel
Mating Retention	With
Mating Retention Type	Mounting Holes
Housing Features	
Housing Color	Black
Housing Material	Nylon GF, Polyester GF
Centerline (Pitch)	2.74 mm, 2.76 mm, 2.79 mm [.108 in][.109 in] [.11 in]
Dimensions	
Cable Insulation Diameter Range	4.7 – 8.13 mm
Wire Size	.2 – .56 mm ²
Usage Conditions	
Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
Operation/Application	
Shielded	Yes
Circuit Application	Signal
Industry Standards	
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Quantity	1
Packaging Method	Kit, Package

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 58448-3 PRO-CRIMPER DIE</p>	 <p>TE Part # 91503-1 CCII AMPLIMITE 20 DF PIN SKT 28-20 ASSY</p>	 <p>TE Part # 58448-2 PRO CR. ASSY AMPLIMITE IS 9357</p>
--	---	---

Documents

Product Drawings

[KIT,HDP-20,PLUG,SIZE 3, 25 POS](#)

English

CAD Files

[3D PDF](#)



English

Customer View Model

[ENG_CVM_749805-9_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_749805-9_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_749805-9_B.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English