


## MICTOR

TE Internal #: 767025-5

PCB Mount Header, Vertical, Board-to-Board, 190 Position, .64 mm  
[.025 in] Centerline, Gold, Surface Mount, Signal, Black[View on TE.com >](#)

Connectors &gt; PCB Connectors &gt; PCB Headers &amp; Receptacles

PCB Connector Assembly Type: **PCB Mount Header**PCB Mount Orientation: **Vertical**Connector System: **Board-to-Board**Number of Positions: **190**Centerline (Pitch): **.64 mm [ .025 in ]****Features****Product Type Features**

Ground Component Type	Ground Bus
PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

**Configuration Features**

Number of Power Positions	5
Number of Columns	95
Stackable	Yes
Number of Signal Positions	190
PCB Mount Orientation	Vertical
Number of Positions	190
Board-to-Board Configuration	Parallel

**Electrical Characteristics**

Insulation Resistance	2 MΩ
Impedance	50 Ω
Operating Voltage	30 VAC

**Signal Characteristics**

Differential Signaling	Yes
------------------------	-----



Data Rate	10 Gb/s
-----------	---------

### Body Features

Primary Product Color	Black
-----------------------	-------

### Contact Features

Contact Layout	Inline
	150 – 250 µin
Contact Shape & Form	Dual Beam
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin-Lead
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Type	Pin
Contact Current Rating (Max)	11.5 A

### Termination Features

Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Termination Method to Printed Circuit Board	Surface Mount

### Mechanical Attachment

PCB Mount Alignment Type	Boardlock, Locating Posts
Mating Retention	With
PCB Mount Retention Type	Boardlock
Mating Alignment	Without
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount

### Housing Features

Centerline (Pitch)	.64 mm[.025 in]
Housing Material	LCP (Liquid Crystal Polymer)

### Dimensions

Connector Length	76.2 mm[3 in]
Connector Height	17.76 mm[.699 in]
Connector Width	8.13 mm[.32 in]



Stack Height	17.96 mm, 27 mm[1.062 in]
--------------	---------------------------

PCB Thickness (Recommended)	1.57 mm[.8 in]
-----------------------------	----------------

### Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

### Operation/Application

Assembly Process Feature	None
--------------------------	------

Circuit Application	Signal
---------------------	--------

### Industry Standards

UL Rating	Listed
-----------	--------

Agency/Standard	CSA, UL
-----------------	---------

Approved Standards	CSA 1195944, UL E28476
--------------------	------------------------

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Quantity	7
--------------------	---

Packaging Type	Box, Tube
----------------	-----------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
------------------------------	---------------

EU ELV Directive 2000/53/EC	Compliant with Exemptions
-----------------------------	---------------------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224)
--	--

Candidate List Declared Against: JUNE 2022 (224)

SVHC > Threshold:

Pb (40% in Component Part)

**Article Safe Usage Statements:**

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---









Solder Process Capability	Reflow solder capable to 260°C
---------------------------	--------------------------------


#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as

EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 <p>TE Part # 2-767004-6 MICT,RECPT,190,ASSY,.025,REC</p>	 <p>TE Part # 1-767096-2 MICT,REC,190,ASY,.025,TAPE,CAP</p>	 <p>TE Part # 1-767114-2 MICT,REC,190,ASY,.025,TAPE PKG</p>	 <p>TE Part # 1-767115-2 MICT,REC,190,ASY,.025 TAPE PKG</p>
 <p>TE Part # 1-767153-2 190 POS. .355 VERTICAL RECEPTA</p>	 <p>TE Part # 1-767178-2 MICTOR RAISED VERT RECPT ASSY,</p>	 <p>TE Part # 767054-5 MICT,RECPT,190,ASSY,PDNI</p>	 <p>TE Part # 767061-5 MICT,RECPT,190,ASSY,093,PDNI</p>
 <p>TE Part # 767081-5 MICT,REC,190,ASY,PDNI,BARBLESS</p>	 <p>TE Part # 767089-5 MICTOR,R/A,RECPT,.093,190,ASY</p>	 <p>TE Part # 767094-5 MICT,RECPT,190,ASY,PDNI,EXTD</p>	 <p>TE Part # 767095-5 MICT,REC,EXT,190,ASY,PDNI,025</p>
 <p>TE Part # 767096-5 MICT,REC,190,ASY,.025,TAPE PKG</p>	 <p>TE Part # 767110-5 MICT,RECPT,190,ASSY,.025</p>	 <p>TE Part # 767114-5 MICT,REC,190,ASY,.025,TAPE,CAP</p>	 <p>TE Part # 767115-5 MICT,REC,190,ASY,.025 TAPE PKG</p>

TE Part # 767130-5  
MICT,RCPT,190,ASY,GOLD,EXTDTE Part # 767143-5  
MICT,R/A,RCPT,190,ASY,062,30AUTE Part # 767154-5  
190 POS. .355 VERTICAL RECEPTEATE Part # 767178-5  
MICTOR RAISED VERT RECPT ASSY,

## Documents

### Product Drawings

[MICT,707PLUG,190,ASSY,.025,REC](#)

English

### CAD Files

[3D PDF](#)

English

Customer View Model

[ENG\\_CVM\\_767025-5\\_P1.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_767025-5\\_P1.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_767025-5\\_P1.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[MICTOR Interconnection System](#)

English

### Product Specifications

[Application Specification](#)

English