

770012-6 ✓ ACTIVE

MATE-N-LOK | Universal MATE-N-LOK

TE Internal #: 770012-6

Power Contacts, Contact, 600 VAC, Gold, 30 – 26 AWG Wire Size, .05 – .13 mm<sup>2</sup> Wire Size, Wire-to-Wire, Wire & Cable, Crimp, Power, Universal MATE-N-LOK

[View on TE.com >](#)



Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**

Operating Voltage: **600 VAC**

Contact Mating Area Plating Material: **Gold**

Wire Size: **.05 – .13 mm<sup>2</sup>**

## Features

### Product Type Features

Power Contact Type	Contact
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

### Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

### Contact Features

Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	7 A
Contact Type	Socket
Contact Retention Within Housing	Without
Mating Pin Diameter	2.2 mm [.086 in]
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material Thickness	.76 μm [30 μin]
Wire Contact Termination Area Plating Thickness	.76 μm [30 μin]
Wire Contact Termination Area Plating Material	Gold



Wire Contact Termination Area Plating Material Finish	Bright
Contact Orientation	Straight
Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]

### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

### Dimensions

Wire Size	.05 – .13 mm <sup>2</sup>
Accepts Wire Insulation Diameter Range	.81 – 1.45 mm[.032 – .057 in]

### Usage Conditions

Operating Temperature Range	-55 – 120 °C[-67 – 248 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	Power
---------------------	-------

### Industry Standards

CSA Rating	Certified
Glow Wire Rating	Standard Part - Not Glow Wire
VDE Tested	Yes
Agency/Standard	CSA, UL
CSA File Number	LR 7189
UL Rating	Recognized
UL File Number	E28476

### Packaging Features

Packaging Method	Reel
Packaging Quantity	5000

### Other

Wire/Cable Type	Discrete Wire
Wire Type	Stranded
For Use With	Standard Universal MATE-N-LOK(Pin)

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 539972-1  
EXTRACTION TOOL



TE Part # 455830-1  
INSERTION TOOL



TE Part # 770019-1  
04P UMNLI IN-LINE PLUG HSG KIT



TE Part # 770028-1  
09P UMNLI IN-LINE CAP HSG KIT



TE Part # 770026-1  
04P UMNLI IN-LINE CAP HSG KIT



TE Part # 770024-1  
02P UMNLI IN-LINE CAP HSG KIT



TE Part # 770029-1  
12P UMNLI IN-LINE CAP HSG KIT



TE Part # 770021-1  
09P UMNLI IN-LINE PLUG HSG KIT



TE Part # 770030-1  
15P UMNLI IN-LINE CAP HSG KIT



TE Part # 770018-1  
03P UMNLI IN-LNE PLUG HSG KIT



TE Part # 770027-1  
06P UMNLI IN-LINE CAP HSG KIT



TE Part # 770025-1  
03P UMNLI IN-LINE CAP HSG KIT



TE Part # 770017-1  
02P UMNLI IN-LNE PLUG HSG KIT



TE Part # 770020-1  
06P UMNLI IN-LNE PLUG HSG KIT



TE Part # 770023-1  
15P UMNLI IN-LNE PLUG HSG KIT



TE Part # 9-1579007-5  
EXTRACTION TOOL




TE Part # 770022-1  
12P UMNLI IN-LNE PLUG HSG KIT




TE Part # 770016-1  
05P UMNLI IN-LNE PLUG HSG KIT


## Also in the Series | Universal MATE-N-LOK




Circular Power Connectors(2)




Connector Contacts(11)



Insertion & Extraction Tools(4)




Power Contacts(207)




Rectangular Boots & Strain Relief(35)



Rectangular Connector Adapters(7)



Rectangular Connector Hardware(1)




Rectangular Connector Housings(2)



Rectangular Connector Keying Plugs(3)



Rectangular Connector Locking(4)



Rectangular Connector Seals(26)



Rectangular Power Connectors(728)

## Documents

### Product Drawings

[UMNL II SOK SELECT AU/PHBZ](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_770012-6\\_G.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_770012-6\\_G.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_770012-6\\_G.3d\\_stp.zip](#)

English

[3D PDF](#)

English

Customer View Model

[ENG\\_CVM\\_770012-6\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_770012-6\\_C.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_770012-6\\_C.2d\\_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[SOFT\\_SHELL\\_PIN\\_SOCKET\\_CONNECTORS\\_STANDARD\\_DENSITY](#)

English

### Product Specifications

[Application Specification](#)



English