



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Wire**

Number of Positions: **9**

Centerline (Pitch): **6.35 mm [.25 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	9
Number of Rows	3

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Contact Layout	Matrix
Multiple Contact Types	Without
Contact Retention Within Housing	Without



Contact Type	Socket
Termination Features	
Termination Method to Wire & Cable	Crimp
Mechanical Attachment	
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Centerline (Pitch)	6.35 mm[.25 in]
Housing Color	White
Housing Material	Nylon
Dimensions	
Row-to-Row Spacing	6.35 mm[.25 in]
Width	20.32 mm
Height	27.43 mm
Length	21.46 mm
Usage Conditions	
Operating Temperature Range	-55 – 120 °C[-67 – 248 °F]
Operation/Application	
Assembly Integration Feature	Without
Circuit Application	Power & Signal
Industry Standards	
CSA Rating	Certified
UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire
Agency/Standard Number	E28476
Agency/Standard	CSA, UL
UL Rating	Recognized
CSA File Number	LR7189
VDE Tested	Yes
Packaging Features	
Packaging Method	Package
Packaging Quantity	1



Other

For Use With	Standard Universal MATE-N-LOK Connectors
--------------	--

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 770028-1 09P UMNLI IN-LINE CAP HSG KIT	 TE Part # 927231-3 HONHUS UMNL V0 9-P	 TE Part # 927231-5 UNML CAP HSG 9WAY	 TE Part # 770039-1 09P UMNLI PLUG-FRONT 94VO
--	---	--	--



TE Part # 1586853-1
09P UMNL CAP HSG, GW



TE Part # 643254-1
09P UMNL ASSY MOD HSG VO



TE Part # 794538-1
09P UMNL CAP HSG 150C BLK



TE Part # 1969882-1
09P UMNL CAP HSG, P/M, GW V0



TE Part # 2029299-1
9 POS UMNL CAP W/LARGE FLANGE-V0



TE Part # 2029315-1
09P UMNL CAP HSG 150C-RED



TE Part # 2029368-1
09P UMNL-II TW-N-LK-CAP FRONT



TE Part # 2029370-1
09P UMNL-II REAR, TW-N-LK-CAP



TE Part # 2178934-1
CAP, 9 CIRCUIT, UMNL,SPECIAL

Also in the Series | Universal MATE-N-LOK




Circular Power Connectors(2)



Connector Contacts(11)




Insertion & Extraction Tools(4)



Power Contacts(207)



Rectangular Boots & Strain Relief(35)



Rectangular Connector Adapters(7)



Rectangular Connector Hardware(1)



Rectangular Connector Housings(2)



Rectangular Connector Keying Plugs(3)



Rectangular Connector Locking(4)



Rectangular Connector Seals(26)



Rectangular Power Connectors(728)

Documents

Product Drawings

09P UMNL II PLUG REAR 94VO

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_770040-1_W.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_770040-1_W.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_770040-1_W.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_770040-1_E.3d_igs.zip

English

Customer View Model

ENG_CVM_770040-1_E.3d_stp.zip

English

Customer View Model

ENG_CVM_770040-1_E.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

Product Specifications

Application Specification



English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Agency Approvals

CSA Certificate

English