



Alcoswitch

TE Internal #: 6-1437624-1

Switch Knobs, Knob, Molded Phenolic Resin, Ribbed Knob Design, 3.17 mm [.125 in] Shaft Size, 14 mm [.551 in] Diameter, Black, Line

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Switch Knobs



Switch Knob Product Type: **Knob**

Switch Knob Material: **Molded Phenolic Resin**

Knob Design: **Ribbed**

Shaft Size: **3.17 mm [.125 in]**

Switch Knob Diameter: **14 mm [.551 in]**

Features

Product Type Features

Switch Knob Product Type	Knob
--------------------------	------

Configuration Features

Skirt	Without
Spinner	Without
Spin Plate	Without
Knob Design	Ribbed

Body Features

Switch Knob Material	Molded Phenolic Resin
Switch Knob Color	Black

Dimensions

Shaft Size	3.17 mm [.125 in]
Switch Knob Diameter	14 mm [.551 in]

Identification Marking

Indicator Style	Line
-----------------	------



Indicator Location

Top & Side

Other

Comment

Top spun aluminum inlay

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)
Candidate List Declared Against: JUNE 2022 (224)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents



Product Drawings

[PKG50B1/8=KNOB PLASTIC 1/8 LEX](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_6-1437624-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-1437624-1_O.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-1437624-1_O.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_6-1437624-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_6-1437624-1_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_6-1437624-1_A.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English