

TERMI-POINT

TE Internal #: 6-330495-2

Power Contacts, Termination Point Clip, Gold, 22 AWG Wire Size, .3 mm² Wire Size, Wire-to-Wire, Wire & Cable, Crimp, Signal, Socket[View on TE.com >](#)

Connectors > Power Connectors > Power Contacts

Power Contact Type: **Termination Point Clip**Contact Mating Area Plating Material: **Gold**Wire Size: **.3 mm²**Connector System: **Wire-to-Wire****Features****Product Type Features**

Power Contact Type	Termination Point Clip
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Contact Features

Contact Mating Area Plating Material	Gold
Contact Type	Socket
Mating Tab Width	1.57 mm[.062 in]
Mating Tab Thickness	.78 mm[.031 in]
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material Thickness	.762 μm[30 μin]
Wire Contact Termination Area Plating Material	Tin-Lead
Contact Orientation	Straight
Contact Underplating Material	Tin

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

PCB Mount Retention	Without
Wire Insulation Support	Without

Dimensions



Wire Size	.3 mm ²
-----------	--------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Identification Marking

Color Code	Orange
------------	--------

Packaging Features

Packaging Method	Clip/Reel
------------------	-----------

Packaging Quantity	1000
--------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2019 (197) Does not contain REACH SVHC
--	--

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

[CLIP T-PT 031 X 062 AU 22 AWG](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_6-330495-2_CJ.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-330495-2_CJ.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-330495-2_CJ.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Products for Aerospace and Defense](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English