

# CES-2-A75 ✓ ACTIVE

RAYCHEM | RAYCHEM CES


TE Internal #: 721041-001

Cable Entry Seals, NPT Threaded, Nylon / Polyolefin, 1 Branches,  
19.1 mm [.75 in] Expanded Inside, 6.4 mm [.25 in] Recovered Inside,  
RAYCHEM CES

[View on TE.com >](#)



Wire Protection & Management > Heat Shrink Shapes > Cable Entry Seals



Cable Entry Seal Seal Type: **NPT Threaded**

Cable Entry Seal Material: **Nylon, Polyolefin**

Number of Branches & Legs: **1**

Expanded Inside Diameter (Min): **19.1 mm [.75 in]**

Recovered Inside Diameter (Max): **6.4 mm [.25 in]**

## Features

### Product Type Features

Angle	Straight
Thread Style	NPT
Product Type	Heat Shrink Cable Entry Seal

### Configuration Features

Number of Branches & Legs	1
---------------------------	---

### Body Features

Cable Entry Seal Seal Type	NPT Threaded
Cable Entry Seal Material	Nylon, Polyolefin

### Mechanical Attachment

Screw & Hole Thread Size	1-3/4-14
--------------------------	----------

### Dimensions

Overall Length (Supplied)	62.23 mm[2.45 in]
Overall Length (Recovered)	62.23 mm[2.45 in]
Expanded Inside Diameter (Min)	19.1 mm[.75 in]
Recovered Inside Diameter (Max)	6.4 mm[.25 in]
Drill Size	.75
Compatible Cable Diameter Range	6.6 – 16.26 mm[.26 – .64 in]

### Usage Conditions



Flammability Requirement	Flame-Retardant
--------------------------	-----------------

**Other**

Comment	Molded part has hot-melt adhesive preinstalled.
---------	---

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**



TE Part # CJ2087-000  
HL2010E-KIT-120V

**Also in the Series | RAYCHEM CES**



Cable Entry Seals(30)



Cable Transitions & Breakouts(3)



Feedthroughs(3)



Heat Shrink Boots(2)

## Documents

### Product Drawings

[CES-2-A75](#)

English

### Datasheets & Catalog Pages

[Raychem Molded Parts Visual Guide](#)

English

### Product Specifications

[Product Specification](#)

English

[Raychem S1297 and /97 Hot Melt Adhesive](#)

English