



Connectors > Terminal Blocks & Strips > PCB Terminal Blocks

Terminal Block Connector Type: **Header**Connector System: **Wire-to-Board**Number of Positions: **9**Centerline (Pitch): **5 mm [.197 in]**Number of Rows: **1**

Features

Product Type Features

| | |
|-----------------------------------|-----------------------|
| Block Type | PCB Mount |
| Header Type | Fully Shrouded |
| Terminal Block Connector Type | Header |
| Connector System | Wire-to-Board |
| Connector & Contact Terminates To | Printed Circuit Board |

Configuration Features

| | |
|---------------------|---------|
| Threaded Flange | Without |
| Closed End | With |
| Number of Positions | 9 |
| Number of Rows | 1 |

Electrical Characteristics

| | |
|----------------------|---------|
| Current Rating (Max) | 15 A |
| Voltage Rating | 300 VAC |

Body Features



| | |
|-----------|---------|
| Interlock | Without |
|-----------|---------|

Contact Features

| | |
|--------------------------------------|--------------|
| Contact Mating Area Plating Material | Tin |
| Contact Mount | Through Hole |
| Contact Base Material | Copper Alloy |
| Contact Current Rating (Max) | 15 A |

Mechanical Attachment

| | |
|--------------------------|-------------|
| Screwless Terminal Block | No |
| Mounting Angle | Right Angle |
| Screw Flange | Without |
| Connector Mounting Type | Board Mount |

Housing Features

| | |
|--------------------|----------------|
| Housing Color | Green |
| Housing Material | PA 66 |
| Centerline (Pitch) | 5 mm [.197 in] |

Dimensions

| | |
|-----------------|-------------------------|
| PCB Tail Length | 3.5 mm [.138 in] |
| Wire Size | .05 – 3 mm ² |

Usage Conditions

| | |
|-----------------------------|-----------------------------|
| Operating Temperature Range | -40 – 105 °C [-40 – 221 °F] |
|-----------------------------|-----------------------------|

Operation/Application

| | |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

Identification Marking

| | |
|---------------|-------|
| Marking Color | White |
|---------------|-------|

Packaging Features

| | |
|--------------------|-----|
| Packaging Method | Box |
| Packaging Quantity | 100 |

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

| | |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
|------------------------------|-----------|



EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 796640-9
9 POS 5.0 MM R/A PLUG, TRM BLK



TE Part # 796641-9
9 POS 5.0 MM R/A PLUG, TRM BLK



TE Part # 1546118-9
9 POS 5.0 MM VERT. PLUG LH BLCK




TE Part # 1546557-9
9P, SCREWLESS CLIP PLUG, 5.0MM



TE Part # 1776148-9
9P TERMI-BLOK HDR, HIGH TEMP



TE Part # 284040-9
TERMI-BLOK VERTICAL PLUG STACK



TE Part # 284046-9
TERMI-BLOK VERTICAL PLUG STACK

Documents

Product Drawings



9POS 5.0MM CE R/A HDR,TRM BLK

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_796644-9_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_796644-9_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_796644-9_C.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_796644-9_C1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_796644-9_C1.2d_dxf.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_796644-9_C1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

BUCHANAN PCB TERMINAL BLOCKS

English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

Product Specifications

Application Specification

English