

745550-1 ✓ ACTIVE

AMPLIMITE | AMPLIMITE Kit


TE Internal #: 745550-1

D-Sub Backshells & Clamps, Cable Clamp Kit, Slide-On Back Cover, 9 Position, Size 1, Cable Exit Angle 90° (Right Angle), AMPLIMITE Kit

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: **Cable Clamp Kit**

Cable Clamp Type: **Slide-On Back Cover**

Number of Positions: **9**

Compatible With Connector Shell Size: **1**

Shielded: **No**

Features

Product Type Features

Grommets	Without
Product Type	Accessory
D-Shaped Connector Accessories	Cable Clamp Kit

Configuration Features

Number of Positions	9
---------------------	---

Body Features

Shield Plating Material	None
Cable Clamp Material	Thermoplastic
Color	Black
Cable Clamp Type	Slide-On Back Cover
Cable Exit Angle	90° (Right Angle)

Mechanical Attachment

Screw & Hole Thread Size	None
--------------------------	------

Dimensions

Cable Insulation Diameter Range	8.38 mm[.33 in]
---------------------------------	-----------------

Operation/Application

Compatible With Connector Shell Size	1
Shielded	No



Packaging Features

Packaging Quantity	1
Packaging Method	Bag

Other

Comment	All parts are packaged unassembled., Each kit is comprised of a cover half and an assortment of cable support gate latches.
---------	---

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | AMPLIMITE Kit



Documents

Product Drawings

[HDE 20 KIT 90 DEG CBL CLMP](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_745550-1_C.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_745550-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_745550-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Cable Connectors](#)

English

[AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG](#)

English

Product Environmental Compliance



[TE Material Declaration](#)

English

[Instruction Sheets](#)

[Instruction Sheet \(U.S.\)](#)

English

[AMPLIMITE HDP-20 AND HDE-20 CONNECTORS THREE-PIECE AND TWO-PIECE](#)

English