

767056-3 ✓ ACTIVE

MICTOR


TE Internal #: 767056-3

PCB Mount Header, Vertical, Board-to-Board, 114 Position, .64 mm [.025 in] Centerline, Gold Flash over Palladium Nickel, Surface Mount, Signal, Black

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **114**

Centerline (Pitch): **.64 mm [.025 in]**

Features

Product Type Features

| | |
|-----------------------------------|-----------------------|
| Ground Component Type | Ground Bus |
| PCB Connector Assembly Type | PCB Mount Header |
| Connector System | Board-to-Board |
| Sealable | No |
| Connector & Contact Terminates To | Printed Circuit Board |

Configuration Features

| | |
|------------------------------|----------|
| Number of Power Positions | 3 |
| Number of Columns | 57 |
| Stackable | Yes |
| Number of Signal Positions | 114 |
| PCB Mount Orientation | Vertical |
| Number of Positions | 114 |
| Board-to-Board Configuration | Parallel |

Electrical Characteristics

| | |
|-----------------------|--------|
| Insulation Resistance | 2 MΩ |
| Impedance | 50 Ω |
| Operating Voltage | 30 VAC |

Signal Characteristics



| | |
|------------------------|-----|
| Differential Signaling | Yes |
|------------------------|-----|

| | |
|-----------|---------|
| Data Rate | 10 Gb/s |
|-----------|---------|

Body Features

| | |
|-----------------------|-------|
| Primary Product Color | Black |
|-----------------------|-------|

Contact Features

| | |
|----------------|--------|
| Contact Layout | Inline |
|----------------|--------|

150 – 250 μ m

| | |
|----------------------|-----------|
| Contact Shape & Form | Dual Beam |
|----------------------|-----------|

| | |
|-------------------------------|--------|
| Contact Underplating Material | Nickel |
|-------------------------------|--------|

| | |
|---|----------|
| PCB Contact Termination Area Plating Material | Tin-Lead |
|---|----------|

| | |
|-----------------------|--------------|
| Contact Base Material | Copper Alloy |
|-----------------------|--------------|

| | |
|--------------------------------------|----------------------------------|
| Contact Mating Area Plating Material | Gold Flash over Palladium Nickel |
|--------------------------------------|----------------------------------|

| | |
|--|------------------------|
| Contact Mating Area Plating Material Thickness | .12 μ m[5 μ m] |
|--|------------------------|

| | |
|--------------|-----|
| Contact Type | Pin |
|--------------|-----|

| | |
|------------------------------|--------|
| Contact Current Rating (Max) | 11.5 A |
|------------------------------|--------|

Termination Features

| | |
|---|----------------|
| Rectangular Termination Post & Tail Thickness | .2 mm[.008 in] |
|---|----------------|

| | |
|---|-----------------|
| Rectangular Termination Post & Tail Width | .53 mm[.021 in] |
|---|-----------------|

| | |
|---|---------------|
| Termination Method to Printed Circuit Board | Surface Mount |
|---|---------------|

Mechanical Attachment

| | |
|--------------------------|----------------|
| PCB Mount Alignment Type | Locating Posts |
|--------------------------|----------------|

| | |
|------------------|------|
| Mating Retention | With |
|------------------|------|

| | |
|------------------|---------|
| Mating Alignment | Without |
|------------------|---------|

| | |
|---------------------|------|
| PCB Mount Retention | With |
|---------------------|------|

| | |
|---------------------|------|
| PCB Mount Alignment | With |
|---------------------|------|

| | |
|-------------------------|-------------|
| Connector Mounting Type | Board Mount |
|-------------------------|-------------|

Housing Features

| | |
|--------------------|-----------------|
| Centerline (Pitch) | .64 mm[.025 in] |
|--------------------|-----------------|

| | |
|------------------|------------------------------|
| Housing Material | LCP (Liquid Crystal Polymer) |
|------------------|------------------------------|

Dimensions

| | |
|------------------|---------------|
| Connector Length | 50.8 mm[2 in] |
|------------------|---------------|

| | |
|------------------|------------------|
| Connector Height | 6.53 mm[.257 in] |
|------------------|------------------|



| | |
|-----------------------------|---------------------------|
| Connector Width | 5.28 mm[.208 in] |
| Stack Height | 6.6 mm, 15.62 mm[.615 in] |
| PCB Thickness (Recommended) | 1.57 mm[.8 in] |

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 125 °C[-67 – 257 °F] |
|-----------------------------|----------------------------|

Operation/Application

| | |
|--------------------------|--------|
| Assembly Process Feature | None |
| Circuit Application | Signal |

Industry Standards

| | |
|------------------------|------------------------|
| UL Rating | Listed |
| Agency/Standard | CSA, UL |
| Approved Standards | CSA 1195944, UL E28476 |
| UL Flammability Rating | UL 94V-0 |

Packaging Features

| | |
|--------------------|-----------|
| Packaging Quantity | 10 |
| Packaging Type | Box, Tube |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Not Compliant |
| EU ELV Directive 2000/53/EC | Not Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (40% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Reflow solder capable to 260°C |

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







TE Part # 767115-3
MICT,REC,114,ASY,.025 TAPE PKG



TE Part # 767130-3
MICT,RCPT,114,ASY,GOLD,EXTD



TE Part # 767143-3
MICT,R/A,RCPT,114,ASY,062,30AU



TE Part # 767145-3
MICTOR .355 EXTENDED HEIGHT
RECEPTACLE,

Documents

Product Drawings

[MICT,260,PLUG,114,ASSY,PDNI](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_767056-3_P.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_767056-3_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_767056-3_P.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[MICTOR Interconnection System](#)

English

Product Specifications

[Application Specification](#)

English