

AMPSEAL

TE Internal #: 776200-1

TE Internal Description: 23POS,PIN DIA 1.3,HDR ASSY,180DEG,
COD 1

AMPSEAL PCB Headers

[View on TE.com >](#)



All AMPSEAL PCB Headers (6)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-AM78-CH8172

[AMPSEAL Receptacle Housings](#)

Also in the Series | AMPSEAL



[Automotive Connector Caps & Covers](#)
(5)



[Automotive Connector Locks & Position Assurance](#)(1)



[Automotive Housings](#)(31)



[Automotive Seals & Cavity Plugs](#)(1)



[Automotive Terminals](#)(8)



[PCB Headers & Receptacles](#)(29)

Documents

Product Drawings

23POS,PIN DIA 1.3,HDR ASSY,180DEG,COD 1

English

CAD Files

Customer View Model

[ENG_CVM_776200-1_D3.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_776200-1_D3.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_776200-1_D3.2d_dxf.zip](#)

English

3D PDF

English



3D PDF

3D

Customer View Model

ENG_CVM_CVM_776200-1_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_776200-1_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_776200-1_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPSEAL Connector Catalog

English

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English